

Project Name

Location

Prepared By



SATCO S29816

15A19/LED/3000K/1600L/120V/D

Notes

(revised) 10-27-2023 09:20:00

General

Status	Active
Watts	15W
Incandescent Equivalent	100W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	3000K
Temperature	Warm White
CRI	80+
Lumens	1600L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	25000
Product Category	Type A
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	0.94
Operating Temperature	-25C (-13F) to +45C (+113F)

Physical

MOL	4.646
MOD	2.362
Housing Color	White
Weight (lb.)	0.11

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5-Years

Compliance

Safety Listing	cULus - Certified; cULus - Listed
Location Rating	Damp
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
California Compliant Substitute	S28653
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp