



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S3713TRW Recp Recess TR 15A/125V W/Wallplate WH

Pass & Seymour/Legrand

Catalog Number	S3713TRW
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Clock Hanger Recessed Receptacle With Smooth Wall Plate 15A, 125V. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page.
Weight per unit	0.2772 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
indoor/outdoor	Indoor
media	Yes
Number of Wires	3
Outlet Type	Tamper-Resistant, Commercial, Indoor
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	5"
------	----

Descriptions

Description	RECP RECESS TR 15A/125V W/WALLPLATE WH
extra long description	P&S S3713TRW RECP RECESS TR 15A/125
Long Description	Tamper-Resistant Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.
Product Type	Recp Recess TR 15A/125V W/Plate WH
Special Features	Dust & moisture resistant, clock hanger receptacle, cellular neoprene sealing mat fits under wall plate

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007180152
Manufacturers Part Number	S3713TRW
UPC	785007180152



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.2772

Uses, Certifications, and Standards

Application	Commercial
Mounting	WALL
nema rating	5-15R
standard	CULUS, UL 498