



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S3713TRW Recp Recess TR 15A/125V W/Wallplate WH

*Pass & Seymour/Legrand*

Catalog Number	S3713TRW
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Clock Hanger Recessed Receptacle With Smooth Wall Plate 15A, 125V. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page.
Weight per unit	0.2772 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	15
indoor/outdoor	Indoor
media	Yes
Number of Wires	3
Outlet Type	Tamper-Resistant, Commercial, Indoor
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	5"
------	----

### Descriptions

Description	RECP RECESS TR 15A/125V W/WALLPLATE WH
extra long description	P&S S3713TRW RECP RECESS TR 15A/125
Long Description	Tamper-Resistant Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.
Product Type	Recp Recess TR 15A/125V W/Plate WH
Special Features	Dust & moisture resistant, clock hanger receptacle, cellular neoprene sealing mat fits under wall plate

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007180152
Manufacturers Part Number	S3713TRW
UPC	785007180152



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.2772

## Uses, Certifications, and Standards

Application	Commercial
Mounting	WALL
nema rating	5-15R
standard	CULUS, UL 498