



# S4881

40A15/TF  
40 watt A15 Incandescent; Frost; 2500 average rated hours;  
265 lumens; Medium base; 130 volts; Shatter Proof

### Features

- Shatterproof coated incandescent
- Vibration service
- Long life
- Brass Base
- 130 volt



S4881

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4881	045923048814	40	A15	Medium	E26	40A15/TF	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost Shatter Proof	3 1/2"	1.88"	C-9	265	2500	500/25	Box

RoHS Compliant							
Yes							



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S4881

40A15/TF  
40 watt A15 Incandescent; Frost; 2500 average rated hours;  
265 lumens; Medium base; 130 volts; Shatter Proof

### Features

- Shatterproof coated incandescent
- Vibration service
- Long life
- Brass Base
- 130 volt



S4881

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4881	045923048814	40	A15	Medium	E26	40A15/TF	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost Shatter Proof	3 1/2"	1.88"	C-9	265	2500	500/25	Box

RoHS Compliant							
Yes							



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

