

## STAINLESS STEEL LB CONDUIT BODY



### Features:


- Manufactured in Type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Solid stainless construction permits easy installation using ordinary hand tools
- The flat back design allows extra wiring capacity
- No package qty. required
- Cover and Gasket set included
- Form 8 style

### Certifications and Compliances:

- UL / cUL 514A Listed
- UL file number \_ E307133
- Article 314 of ANSI/NFPA 70, "National Electrical Code" (NEC)
- Approved for Wet Locations (when installed with Cover and Gasket)

### Material:

Body - 316SS  
Gasket - Neoprene  
Cover and Screws: 316SS



### Applications:

To connect and change direction of conduit runs. Can be used as pulling fittings. Accessible wiring chamber provides a spacious location to make splices.

### Industries Commonly Served:

- Food & Beverage Production
- Marine & Coastal Facilities
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical
- Pulp & Paper Mills
- Along with other corrosive environments

Part Number	Trade Size	A	B	C	a	Cubic Inches	Weight (each) Per lb.
S60500LB00	1/2"	5.132"	1.320"	2.510"	4.320"	4"	0.95
S60700LB00	3/4"	5.739"	1.550"	2.929"	4.950"	7"	1.25
S61000LB00	1"	6.680"	1.750"	3.250"	5.650"	11"	1.80
S61200LB00	1-1/4"	7.635"	2.170"	3.925"	6.530"	20"	2.90
S61500LB00	1-1/2"	8.868"	2.530"	4.150"	7.810"	35"	4.25
S62000LB00	2"	11.274"	3.460"	4.478"	10.00"	71"	7.75
S62500LB00	2-1/2"	13.612"	4.650"	6.237"	12.00"	157"	13.10
S63000LB00	3"	13.695"	4.650"	6.320"	12.00"	177"	13.75
S64000LB00	4"	16.420"	5.850"	7.770"	14.63"	380"	29.25

*All dimensions are for informational purposes only \*Tolerances +/- 5%*