



# S7007

500BR40FL/POOL  
500 watt BR40 Incandescent; Frost; 2000 average rated hours;  
5500 lumens; Medium base; 130 volts

### Features

- Pool Lamp
- Brass base prevents freezing in the socket
- Heat resistant glass
- 130 volts



S7007

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S7007	045923070075	500	BR40	Medium	E26	500BR40FL/POOL	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frosted	6 1/2"	5.00"	CC-9/1	5500	2000	24/12	Box

RoHS Compliant
Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S7007

500BR40FL/POOL  
500 watt BR40 Incandescent; Frost; 2000 average rated hours;  
5500 lumens; Medium base; 130 volts

### Features

- Pool Lamp
- Brass base prevents freezing in the socket
- Heat resistant glass
- 130 volts



S7007

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S7007	045923070075	500	BR40	Medium	E26	500BR40FL/POOL	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frosted	6 1/2"	5.00"	CC-9/1	5500	2000	24/12	Box

RoHS Compliant
Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

