



# S7241

23R40/27  
23 watt; R40 Compact Fluorescent; 2700K; 82 CRI; Medium base; 120 volts

### Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7241

| Item Number  | UPC           | Voltage                       | Watts          | Incandescent Equivalent | Lamp Shape       | Base                           | ANSI Base |
|--------------|---------------|-------------------------------|----------------|-------------------------|------------------|--------------------------------|-----------|
| S7241        | 045923072413  | 120                           | 23             | 85W                     | R40              | Medium                         | E26       |
| Lamp Code    | MOL In Inches | MOD In Inches                 | Initial Lumens | Average Rated Hours     | Kelvin Temp      | Color                          | Pack      |
| 23R40/27     | 6.49"         | 5.00"                         | 1090           | 10000                   | 2700             | Warm White                     | 24/6      |
| Package Type | CRI           | CEC Status                    | Hg Content     | RoHS Compliant          | UL or ETL Listed | Warranty                       |           |
| Box          | 82            | Lawful for sale in California | 1.6 mg         | Yes                     | Yes              | <a href="#">2 Year Limited</a> |           |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S7241

23R40/27  
23 watt; R40 Compact Fluorescent; 2700K; 82 CRI; Medium base; 120 volts

### Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7241

| Item Number  | UPC           | Voltage                       | Watts          | Incandescent Equivalent | Lamp Shape       | Base                           | ANSI Base |
|--------------|---------------|-------------------------------|----------------|-------------------------|------------------|--------------------------------|-----------|
| S7241        | 045923072413  | 120                           | 23             | 85W                     | R40              | Medium                         | E26       |
| Lamp Code    | MOL In Inches | MOD In Inches                 | Initial Lumens | Average Rated Hours     | Kelvin Temp      | Color                          | Pack      |
| 23R40/27     | 6.49"         | 5.00"                         | 1090           | 10000                   | 2700             | Warm White                     | 24/6      |
| Package Type | CRI           | CEC Status                    | Hg Content     | RoHS Compliant          | UL or ETL Listed | Warranty                       |           |
| Box          | 82            | Lawful for sale in California | 1.6 mg         | Yes                     | Yes              | <a href="#">2 Year Limited</a> |           |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

