

Project Name

Location

Prepared By



# SATCO S8033R1

48FT/LED/SL/S14/IRR/RGBTW/120V

**Notes**

[www] 18-17-2023 09:20:00

**General**

Status	Active
Finish	Black
Wattage	4W
CCT (Kelvin)	3000K-6500K
Color Temperature	RGB and Tunable White
Indoor or Outdoor Fixture	Indoor and Outdoor

**Smart Product Info**

IOT Enabled	No
Integrated Camera	No

**Specifications**

Technology	LED
CRI	83
Lumen Output	150L
Rated Hours	30000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Dimmable with Remote
Beam Angle	320
Operating Temperature	-20C (-4F) to +45C (+113F)
Weight (lb.)	5.25
Fixture Material	PVC
Fixture Type	String Light
Max. Connectable Units	4

**Compliance**

Safety Listing	cETLus - Listed
Location Rating	Wet
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B

**Additional Information**

Includes	Infrared Remote
Warranty	1-Year

Project Name

Location

Prepared By



# SATCO S8033R1

48FT/LED/SL/S14/IRR/RGBTW/120V

**Notes**

[www] 18-17-2023 09:20:00

**General**

Status	Active
Finish	Black
Wattage	4W
CCT (Kelvin)	3000K-6500K
Color Temperature	RGB and Tunable White
Indoor or Outdoor Fixture	Indoor and Outdoor

**Smart Product Info**

IOT Enabled	No
Integrated Camera	No

**Specifications**

Technology	LED
CRI	83
Lumen Output	150L
Rated Hours	30000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Dimmable with Remote
Beam Angle	320
Operating Temperature	-20C (-4F) to +45C (+113F)
Weight (lb.)	5.25
Fixture Material	PVC
Fixture Type	String Light
Max. Connectable Units	4

**Compliance**

Safety Listing	cETLus - Listed
Location Rating	Wet
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B

**Additional Information**

Includes	Infrared Remote
Warranty	1-Year