



S8325

CFD26W/827
26 watt; pin-based Compact Fluorescent; 2700K; 82 CRI; G24d-3 base

Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8325

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | MOL In Inches |
|----------------|---------------------|-------------|------------|--------|--------------|------------|----------------|
| S8325 | 045923083259 | 26 | T4 | G24d-3 | G24d-3 | CFD26W/827 | 6.8" |
| Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack | Package Type | CRI | RoHS Compliant |
| 1825 | 12000 | 2700 | Warm White | 50 | Hang Box | 82 | Yes |
| UL Listed | | | | | | | |
| Yes | | | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8325

CFD26W/827
26 watt; pin-based Compact Fluorescent; 2700K; 82 CRI; G24d-3 base

Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8325

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | MOL In Inches |
|----------------|---------------------|-------------|------------|--------|--------------|------------|----------------|
| S8325 | 045923083259 | 26 | T4 | G24d-3 | G24d-3 | CFD26W/827 | 6.8" |
| Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack | Package Type | CRI | RoHS Compliant |
| 1825 | 12000 | 2700 | Warm White | 50 | Hang Box | 82 | Yes |
| UL Listed | | | | | | | |
| Yes | | | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

