



# S8436

F32T8/865/ENV  
32 watt; T8; Fluorescent; 6500K Daylight; 82 CRI; Medium Bi  
Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8436

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8436	045923084362	32	T8	Medium Bi Pin	G13	F32T8/865/ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
47.78"	48"	2850	2700	24000	6500	Daylight	30
CRI	RoHS Compliant						
82	Yes						



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8436

F32T8/865/ENV  
32 watt; T8; Fluorescent; 6500K Daylight; 82 CRI; Medium Bi Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8436

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8436	045923084362	32	T8	Medium Bi Pin	G13	F32T8/865/ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
47.78"	48"	2850	2700	24000	6500	Daylight	30
CRI		RoHS Compliant					
82		Yes					



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

