



15 watt PAR38 LED; 3500K; 40' beam spread; Medium base;
120 volts

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

- Lutron® C.L Family of dimmers Gen 2.0-2.1-2.2
- Lutron® MAESTRO MACL-153
- Lutron® CASETEA PPD-6WCL-WH



S9447

Item Number	UPC		Voltage	Watts	Incandescent Equivalent		Lamp Shape	Base	ANSI Base	
S9447	045923094477		120	15	90W		PAR38	Medium	E26	
Lamp Code			Dimmable/Non-Dimmable		Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
			Dimmable		Silver	5 3/16"	4 3/4"	1150	25000	3500
Color	CRI	Beam Spread Deg	Pack	Package Type		ENERGY STAR	RoHS Compliant		UL or ETL Listed	
Neutral White	80	40	12/6	Box		ENERGY STAR	Yes		Yes	
Warranty										
3 Year Limited										



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051



15 watt PAR38 LED; 3500K; 40' beam spread; Medium base;
120 volts

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

- Lutron® C.L Family of dimmers Gen 2.0-2.1-2.2
- Lutron® MAESTRO MACL-153
- Lutron® CASETEA PPD-6WCL-WH



S9447

Item Number	UPC		Voltage	Watts	Incandescent Equivalent		Lamp Shape	Base	ANSI Base	
S9447	045923094477		120	15	90W		PAR38	Medium	E26	
Lamp Code			Dimmable/Non-Dimmable		Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
			Dimmable		Silver	5 3/16"	4 3/4"	1150	25000	3500
Color	CRI	Beam Spread Deg	Pack	Package Type		ENERGY STAR	RoHS Compliant		UL or ETL Listed	
Neutral White	80	40	12/6	Box		ENERGY STAR	Yes		Yes	
Warranty										
3 Year Limited										



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051