



S9497

6.5MR16/LED/40'/35K/12V
6.5 watt; LED MR16 LED; 3500K; 40' beam spread; GU5.3 base; 12 volts

Features

- Silver back MR16 reflector
- Direct replacement for 50watt Halogen lamps
- Approved for enclosed fixtures
- Dimmable

Compatible Dimmers

- Lutron® SELV300 ELV - Use with electronic low-voltage transformer
- Lutron® SLV600P (MLV) - Use with magnetic low-voltage transformer



S9497

| Item Number | UPC | Voltage | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | |
|-----------------------|-----------------|---------------|----------------|----------------|---------------------|-------------|--------------------------------|--|
| S9497 | 045923094972 | 12 | 6.5 | MR16 | GU5.3 | GU5.3 | 6.5MR16/LED/40'/35K/12V | |
| Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | |
| Dimmable | White | 1 3/4" | 2" | 530 | 25000 | 3500 | Neutral White | |
| CRI | Beam Spread Deg | Pack | RoHS Compliant | | UL or ETL Listed | | Warranty | |
| 80 | 40 | 12/48 | Yes | | Yes | | 3 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9497

6.5MR16/LED/40'/35K/12V
6.5 watt; LED MR16 LED; 3500K; 40' beam spread; GU5.3 base; 12 volts

Features

- Silver back MR16 reflector
- Direct replacement for 50watt Halogen lamps
- Approved for enclosed fixtures
- Dimmable

Compatible Dimmers

- Lutron® SELV300 ELV - Use with electronic low-voltage transformer
- Lutron® SLV600P (MLV) - Use with magnetic low-voltage transformer



S9497

| Item Number | UPC | Voltage | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | |
|-----------------------|-----------------|---------------|----------------|----------------|---------------------|-------------|--------------------------------|--|
| S9497 | 045923094972 | 12 | 6.5 | MR16 | GU5.3 | GU5.3 | 6.5MR16/LED/40'/35K/12V | |
| Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | |
| Dimmable | White | 1 3/4" | 2" | 530 | 25000 | 3500 | Neutral White | |
| CRI | Beam Spread Deg | Pack | RoHS Compliant | | UL or ETL Listed | | Warranty | |
| 80 | 40 | 12/48 | Yes | | Yes | | 3 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

