



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SBR10 15W Led T10 48" W/Battery Backup 35K/4K/5K Plastic *Rab Lighting*

Catalog Number	SBR10
Manufacturer	Rab Lighting
Description	Rab SBR10 T10 Retrofit Tube Fixture
Weight per unit	1.2 (lbs/each)
Product Category	Lighting

Features

average life	50000
Ballast Type	UL Type B, Ballast Bypass
Base	Hardwired
beam angle	140
Fixture Type	Linear Tubes
lumens	1,750/1,800,1,800
Shape	T10
total harmonic distortion	=20%+5%
Wattage	14.5

Material, Color, and Finish

Color	White
color rendering index (cri)	=80
color temperature	3500/4000/5000
Finish	Matte

Dimensions and Weight

Length	48
--------	----

Descriptions

Description	15W LED T10 48" W/BATTERY BACKUP 35K/4K/5K PLASTIC
Long Description	RAB SBR10 T10 RETROFIT TUBE FIXTURE
Product Type	T10 Retrofit Tube Fixture UI924
Special Features	True UL 924 certified LED Retrofit tube that is hardwired 24/7 to main powerBypass the ballast, driver integrated directly into the lamp body3 selectable color temperaturesBackup battery provides up to 200-minutes of emergency illuminationEasy to install, simply remove existing sockets from fixture and wire tube directly

Manufacturer Information

Brand	Rab Lighting
GTIN	00192552037051
Manufacturers Part Number	SBR10
UPC	192552037051



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Tubes

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	1.2

Uses, Certifications, and Standards

Application	Indoor Lamps
-------------	--------------