

Specifications



Eaton SFDN225

Eaton enclosed circuit breaker, 125-225A, Series C, NEMA 1, FD, FDB, HFD, FDC, ED, EDH, EDC, FDC (15-225A), Surface

General specifications

PRODUCT NAME	Eaton enclosed circuit breaker
CATALOG NUMBER	SFDN225
UPC	786679002339
PRODUCT LENGTH/DEPTH	6.28 in
PRODUCT HEIGHT	23.25 in
PRODUCT WIDTH	8.56 in
PRODUCT WEIGHT	15 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	With knockouts.
GLOBAL CATALOG	SFDN225

Product specifications

AMPERAGE RATING	125-225A
CIRCUIT BREAKER TYPE	FD, FDB, HFD, FDC, ED, EDH, EDC, FDC
ENCLOSURE	NEMA 1
SERIES	Series C
MOUNTING METHOD	Surface mounting
TYPE	Circuit Breaker Enclosure

Resources

CATALOGS	Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SFDN225

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

