

Seoprene 105°C - Black Portable Cord

UL Listed – Flexible and tough jacket. Offers a wide useable temperature range of -50°C to 105°C. Seoprene provides excellent abrasion, ozone, sunlight, chemical, oil, water, and mold resistance along with non-wicking lightweight polypropylene fillers. Water resistant with high dielectric insulation. Lightweight, long lasting, easy to carry and handle. All components are recyclable and non-hazardous for environmental landfill disposal. Federal and Military use under Federal Spec. JC-580B. UL Listed SE00W 600V and SJEOOW 300V to NEC Article 400, CSA approved ST00W or SJTOOW (TPE) -50°C to 105°C. MSHA approved for flame resistance in mining applications.



PART NO	SIZE	TYPE	JACKET COLOR	PKG WT	LENGTH IN FT
23285-04-08	18/2	SJEW	Black	11	250
23385-04-08	18/3	SJEW	Black	14	250
23286-04-08	16/2	SJEW	Black	14	250
23386-04-08	16/3	SJEW	Black	17	250
23486-04-08	16/4	SJEW	Black	20	250
23287-04-08	14/2	SJEW	Black	17	250
23387-04-08	14/3	SJEW	Black	21	250
23487-04-08	14/4	SJEW	Black	26	250
23288-04-08	12/2	SJEW	Black	24	250
23388-04-08	12/3	SJEW	Black	31	250
23488-04-08	12/4	SJEW	Black	39	250
23389-66-08	10/3	SJEW	Black	22	100
23225-04-08	18/2	SJEOOW	Black	11	250
23325-04-08	18/3	SJEOOW	Black	14	250
23425-04-08	18/4	SJEOOW	Black	17	250
23226-04-08	16/2	SJEOOW	Black	14	250
23326-04-08	16/3	SJEOOW	Black	17	250
23426-04-08	16/4	SJEOOW	Black	20	250
23227-04-08	14/2	SJEOOW	Black	17	250
23327-04-08	14/3	SJEOOW	Black	21	250
23427-04-08	14/4	SJEOOW	Black	26	250
23228-04-08	12/2	SJEOOW	Black	25	250
23328-04-08	12/3	SJEOOW	Black	31	250
23428-04-08	12/4	SJEOOW	Black	40	250
23229-04-08	10/2	SJEOOW	Black	42	250
23329-04-08	10/3	SJEOOW	Black	54	250
23429-05-08	10/4	SJEOOW	Black	69	500
22225-04-08	18/2	SE00W	Black	15	250
22325-04-08	18/3	SE00W	Black	18	250
22226-04-08	16/2	SE00W	Black	18	250
22326-04-08	16/3	SE00W	Black	21	250
22227-05-08	14/2	SE00W	Black	63	500
22327-05-08	14/3	SE00W	Black	75	500
22427-05-08	14/4	SE00W	Black	92	500
22228-05-08	12/2	SE00W	Black	82	500
22328-05-08	12/3	SE00W	Black	100	500
22428-05-08	12/4	SE00W	Black	121	500
22229-05-08	10/2	SE00W	Black	104	500
22329-05-08	10/3	SE00W	Black	130	500
22429-05-08	10/4	SE00W	Black	158	500
22320-04-08*	8/3	SE00W	Black	83	250
22420-04-08*	8/4	SE00W	Black	107	250
22321-04-08*	6/3	SE00W	Black	119	250
22421-04-08*	6/4	SE00W	Black	149	250

* Not UL Listed or CSA approved

Bulk Vinyl Portable Cords

UL Listed – A firm compact cylindrical cord cabled for maximum flexibility and roundness per UL 62. Easy to remove jacket. Rated -20°C to 60°C. PVC cords provide excellent abrasion, ozone and chemical resistance. UL Listed and CSA approved 300V SJTW cable for use in cord sets.

PART NO	SIZE	TYPE	JACKET COLOR	PKG WT	LENGTH IN FT
20205-66-03	18/2	SJTW	Orange	11	250
20305-66-03	18/3	SJTW	Orange	13	250
20206-66-03	16/2	SJTW	Orange	13	250
20306-66-03	16/3	SJTW	Orange	16	250
20307-66-03	14/3	SJTW	Orange	21	250
20308-66-03	12/3	SJTW	Orange	31	250
20309-04-03	10/3	SJTW	Orange	56	250