

SL2531 -- Air Tool Oil, 15 Fl Oz



Product Description

A special lubricant designed for pneumatic equipment and tools.

Product Specifications

Applications	Impact wrenches, air ratchets, sanders, grinders, air motors, hammers, drills, etc.
Unit Package Description	15 Ounce Bottle
Brand	Sta-Lube
Generic Description 1	Air Tool Oil
Net Fill	15 Fl Oz
UPC Code	0 72213 25310 8
Unit Dimensions-Inches	9H x 1.63W x 3.75D
Units Per Case	12
Case Dimensions-Inches	9.75H x 8.5W x 11.5D
Cases Per Pallet	133
Lbs. Per Case	13
I 2 of 5 Code	30072213253109
Appearance	Amber Viscous Liquid
Odor	Faint Petroleum
Flashpoint - TCC Method	>300°F
Specific Gravity	0.91
Flammability	Non-flammable
Plastic Safe	Yes
Evaporation Rate	<1 (butyl acetate=1)
ISO Viscosity Grade	22
Working Temp [Degrees F]	-20 to 225°F
DOT Proper Shipping Name	Not Regulated
VOC % (Federal)	0
VOC g/L (Federal)	0
VOC Lbs./Gal. (Federal)	0
VOC Compliant For CA	Not Regulated
VOC Compliant For OTC/ LADCO	Not Regulated
VOC Category/Limit	Not Regulated

SL2531 -- Air Tool Oil, 15 Fl Oz



Product Description

A special lubricant designed for pneumatic equipment and tools.

Product Specifications

Applications	Impact wrenches, air ratchets, sanders, grinders, air motors, hammers, drills, etc.
Unit Package Description	15 Ounce Bottle
Brand	Sta-Lube
Generic Description 1	Air Tool Oil
Net Fill	15 Fl Oz
UPC Code	0 72213 25310 8
Unit Dimensions-Inches	9H x 1.63W x 3.75D
Units Per Case	12
Case Dimensions-Inches	9.75H x 8.5W x 11.5D
Cases Per Pallet	133
Lbs. Per Case	13
I 2 of 5 Code	30072213253109
Appearance	Amber Viscous Liquid
Odor	Faint Petroleum
Flashpoint - TCC Method	>300°F
Specific Gravity	0.91
Flammability	Non-flammable
Plastic Safe	Yes
Evaporation Rate	<1 (butyl acetate=1)
ISO Viscosity Grade	22
Working Temp [Degrees F]	-20 to 225°F
DOT Proper Shipping Name	Not Regulated
VOC % (Federal)	0
VOC g/L (Federal)	0
VOC Lbs./Gal. (Federal)	0
VOC Compliant For CA	Not Regulated
VOC Compliant For OTC/LADCO	Not Regulated
VOC Category/Limit	Not Regulated