



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SP10 Vynylink 12-10 Splice

Burndy LLC

Catalog Number	SP10
Manufacturer	Burndy LLC
Description	Copper Splice, 12-10 Awg, 1.23" Splice Length, Vinyl Insulated.
Weight per unit	0.0070 (lbs/each)
Product Category	Small Terminals & Connectors

Features

insulation	Y
Insulation Type	Vinyl
Material	Copper
pallet quantity	99999

Material, Color, and Finish

Color Code	YELLOW
------------	--------

Descriptions

Description	VINYLINK 12-10 SPLICE
extra long description	BUR SP10 SPLICE- 12- 10 AWG-VINYL
Long Description	Copper Splice, 12-10 AWG, 1.23" Splice Length, Vinyl Insulated.
Product Type	Splice
Special Features	Features: The Type SP VINYLINK Is A PVC Insulated Seamless Butt Splice, Type SP VINYLINK Is Designed To Accommodate A Broad Range Of 600 Volt Cables, Manufactured From Seamless Electrolytic Copper Tubing: Provides Maximum Conductivity And Tensile Strength, In A High Quality Design With NO Seams To Split, Funnel Entry: Provides Easy Wire Insertion, Electro-Tin Plated: Provides Durable Long Lasting Resistance To Corrosion, Expanded Insulation Support: Lower Inventory Requirements, Red Wire Range Of 22-16: Lo

Manufacturer Information

Brand	BURNDY
GTIN	00781810710012
Manufacturers Part Number	SP10
UPC	781810710012

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	SP

Packaging

Carton	40
Weight Per each	0.007



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	For Accommodating A Broad Range Of 600 Volt Cables
standard	Buy American Act Compliant (All status valid till December 2024)
Temperature Rating	105° C