



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SPM7L 1, 2/0 Service Post Connector 1/2 X 1-1/4

Nsi Industries

Catalog Number	SPM7L
Manufacturer	Nsi Industries
Description	Service Post Connector, #1 Awg (Solid);2/0 Awg (Stranded) Conductor Size, Non-Insulated, Copper Conductor Material, 1 Conductor, +90 °C Operating Temperature, 1-1/4 In (Stud) Overall Length, 600 V Ac, 2.76 LB/Ea
Weight per unit	2.8 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	1
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	1 SOL - 2/0 STR
Wire Type	Class A & B

Material, Color, and Finish

Color	Copper
Finish	COPPER

Dimensions and Weight

Size	Stud=1/2 x 13-1 1/4 - Hex Nut=7/8 x 14
------	----------------------------------------

Descriptions

Description	1, 2/0 SERVICE POST CONNECTOR 1/2 X 1-1/4
extra long description	NSI SPM-7L Service Post One Wire 1-
Features	Service Post Connector - One Wire Type 2/0 AWG Service Post Connectors is used for connecting one or two conductors. Made from high copper content hard-drawn rod. Lay-in feature makes them excellent for continuous loop grounding and bonding. Used to ground to bar or plate. Suitable for direct burial in earth or concrete.

Manufacturer Information

GTIN	00662381021069
UPC	662381021069

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Service Post Connectors



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	6
Weight Per each	2.76

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B
Temperature Rating	90 C