


# STP

## LED Step Light

Project

Catalog

Type



### Product Description

NICOR's LED Step Lights are a great complement for your residential and commercial projects. This step light not only provides a touch of safety, but it offers a warm, natural glow making it a perfect accent for any project. For a truly customizable choice, this LED step light offers paintable faceplates making them versatile for any application. Wet location approved for indoor and outdoor use.

**Construction**  
Stamped aluminum faceplates  
High efficiency, fully sealed, maintenance-free LED chamber

**Optical System**  
Louver to conceal LEDs and provide a unique light distribution pattern

**Electrical**  
Long-life LED system coupled with electrical driver to deliver optimal performance per watt  
Operating temperature rating of -10°F to 122°F (-23°C to 50°C)  
TM-21 Projected L70(6k) life 50,000 hours  
Input voltage of 120V

**Mounting and installation**  
Mounts directly in a Non-Metallic 1-Gang box  
Modular design allows fixture to be mounted in horizontal or vertical orientation  
Wet location approved for indoor and outdoor use

**Finish**  
White powder coat finish

**Options**  
May be mounted in vertical (as provided from factory) or horizontal orientation  
Available in White, Black and Oil-Rubbed Bronze, in both Vertical and Horizontal *(White vertical faceplate included)*

**Warranty**  
5-year limited system warranty standard

### PRODUCT INFORMATION

<b>Color Temperature:</b>	2700K
<b>LED Lifetime Projected (Hrs):</b>	50,000
<b>Input Voltage (V):</b>	120V
<b>Power Draw (W)</b>	1W
<b>Trim Height:</b>	4.5 in (114 mm)
<b>Trim Width:</b>	2.75 in (69.85 mm)
<b>Fixture Depth:</b>	2 in (51 mm)



### Ordering Information

Example: STP-10-120-WH

Series	Version	Voltage	Color
STP	10	120	WH

### Faceplate Ordering Information

Horizontal		
FPHBK (Black)	FPHOB (Oil-Rubbed Bronze)	FPHWH (White)
Vertical		
FPVBK (Black)	FVVOB (Oil-Rubbed Bronze)	


# STP

## LED Step Light

Project

Catalog

Type



### Product Description

NICOR's LED Step Lights are a great complement for your residential and commercial projects. This step light not only provides a touch of safety, but it offers a warm, natural glow making it a perfect accent for any project. For a truly customizable choice, this LED step light offers paintable faceplates making them versatile for any application. Wet location approved for indoor and outdoor use.

**Construction**  
Stamped aluminum faceplates  
High efficiency, fully sealed, maintenance-free LED chamber

**Optical System**  
Louver to conceal LEDs and provide a unique light distribution pattern

**Electrical**  
Long-life LED system coupled with electrical driver to deliver optimal performance per watt  
Operating temperature rating of -10°F to 122°F (-23°C to 50°C)  
TM-21 Projected L70(6k) life 50,000 hours  
Input voltage of 120V

**Mounting and installation**  
Mounts directly in a Non-Metallic 1-Gang box  
Modular design allows fixture to be mounted in horizontal or vertical orientation  
Wet location approved for indoor and outdoor use

**Finish**  
White powder coat finish

**Options**  
May be mounted in vertical (as provided from factory) or horizontal orientation  
Available in White, Black and Oil-Rubbed Bronze, in both Vertical and Horizontal *(White vertical faceplate included)*

**Warranty**  
5-year limited system warranty standard

### PRODUCT INFORMATION

<b>Color Temperature:</b>	2700K
<b>LED Lifetime Projected (Hrs):</b>	50,000
<b>Input Voltage (V):</b>	120V
<b>Power Draw (W)</b>	1W
<b>Trim Height:</b>	4.5 in (114 mm)
<b>Trim Width:</b>	2.75 in (69.85 mm)
<b>Fixture Depth:</b>	2 in (51 mm)



### Ordering Information

Example: STP-10-120-WH

Series	Version	Voltage	Color
STP	10	120	WH

### Faceplate Ordering Information

Horizontal		
FPHBK (Black)	FPHOB (Oil-Rubbed Bronze)	FPHWH (White)
Vertical		
FPVBK (Black)	FVOB (Oil-Rubbed Bronze)	