

# Eaton SVX125A1-4A1N1

Catalog Number: SVX125A1-4A1N1

Eaton SVX adjustable frequency drive, 125HP, NEMA Type 1/IP21, 480V, FR8, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton SVX adjustable frequency drive	SVX125A1-4A1N1
<b>UPC</b>	<b>Product Length/Depth</b>
782116011599	13.5 in
<b>Product Height</b>	<b>Product Width</b>
30.1 in	11.5 in
<b>Product Weight</b>	<b>Warranty</b>
127 lb	2 year
<b>Certifications</b>	
IEC 61800-2	
UL 508C	
EN 61800-3 Level H	

## Product specifications

[Brake chopper](#)

No brake chopper

[Modification](#)

Standard boards

[Horsepower](#)

125 hp

[Frame size](#)

8

[Keypad](#)

Alphanumeric

[Input](#)

EMC H

Three-phase

[Rating](#)

NEMA 1, IP21

[Software](#)

Standard

## Resources

[Application notes](#)

[SPI - Variable frequency drives with a common DC bus](#)

[Connecting drives to generator supplies](#)

[Electromagnetic compatibility \(EMC\)](#)

[Brochures](#)

[SVX9000 Adjustable Frequency Drives Brochure](#)

[SVX9000 Adjustable Frequency Drives Product Aid](#)

[Catalogs](#)

[Product Range Catalog Drives Engineering](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - SVX125A1-4A1N1](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)