

Specifications



Photo is representative



Eaton T20P11S10CU

General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, Single-phase, PV: 240 X 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN X 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 150°C, 10 kVA, Cu windings , Frame: 815, uses WS15

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	T20P11S10CU
UPC	786680065156
PRODUCT LENGTH/DEPTH	15.82 in
PRODUCT HEIGHT	30.25 in
PRODUCT WIDTH	16.87 in
PRODUCT WEIGHT	182 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Physical Attributes

COIL MATERIAL	Copper
DESIGN	DS-3
FRAME	815
TAP SIZE	1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN
TYPE	Dry Type Distribution Transformer

Miscellaneous

WEATHERSHIELD	WS15
----------------------	------

Performance Ratings

FREQUENCY RATING	60 Hz
KVA RATING	10 kVA
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	150 °C rise

Resources

CATALOGS	Commercial Distribution Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - T20P11S10CU

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton T20P11S10CU

General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, Single-phase, PV: 240 X 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN X 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 150°C, 10 kVA, Cu windings , Frame: 815, uses WS15

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	T20P11S10CU
UPC	786680065156
PRODUCT LENGTH/DEPTH	15.82 in
PRODUCT HEIGHT	30.25 in
PRODUCT WIDTH	16.87 in
PRODUCT WEIGHT	182 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Physical Attributes

COIL MATERIAL	Copper
DESIGN	DS-3
FRAME	815
TAP SIZE	1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN
TYPE	Dry Type Distribution Transformer

Miscellaneous

WEATHERSHIELD	WS15
----------------------	------

Performance Ratings

FREQUENCY RATING	60 Hz
KVA RATING	10 kVA
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	150 °C rise

Resources

CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - T20P11S10CU

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

