



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC2R HSG-TC Remodel

Lithonia Lighting - Acuity

Catalog Number	TC2R
Manufacturer	Lithonia Lighting - Acuity
Description	The Remodel Housing Is Ideal For Applications Where The Backside Of The Ceiling Is Not Accessible. The Housing Features Adjustable Height to Allow Installation Where Vertical Spacing Is Limited. The Non-Ic Housing Is Designed to Be Installed In Non-Insulated Areas or Where Insulation Is Spaced At Least 3-Inches From The Housing.
Weight per unit	2.8 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	Round

Dimensions and Weight

Height	8
Length	14
Width	8

Descriptions

Construction	Remodel
Description	HSG-TC REMODEL
extra long description	LITH TC2R 6IN Incandescent Remodel
Long Description	The remodel housing is ideal for applications where the backside of the ceiling is not accessible. The housing features adjustable height to allow installation where vertical spacing is limited. The non-IC housing is designed to be installed in non-insulated areas or where insulation is spaced at least 3-inches from the housing.
Product Type	Housing

Manufacturer Information

Brand	Juno Lighting Group
GTIN	00661209017970
Manufacturers Part Number	TC2R
UPC	661209017970

Trade Size

aperture size	6 in
---------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight	5
Weight Per each	2.77

Uses, Certifications, and Standards

Application	Residential
environmental conditions	Indoor
Mounting	Recessed
standard	cUL,UL