



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TC612 3/4" Emt Concrete Tight D/C Coupling

*Appleton/Oz Gedney*

Catalog Number	TC612
Manufacturer	Appleton/Oz Gedney
Description	Features:Concretetight, Application:Dry/Damp Location, Standard:UL 514B, Csa C22.2, Nema FB-1, Trade Size:0.75IN, Outside Diameter:1.21IN, Length:1.78IN, Material:Zinc Die Cast
Weight per unit	0.1600 (lbs/each)
Product Category	Die Cast Compression Emt CPLG

### Features

Connector Type	Compression
Material	Zinc Die Cast
outside diameter	1.21

### Material, Color, and Finish

Color	Metallic
-------	----------

### Dimensions and Weight

Length	1.78
--------	------

### Descriptions

Description	3/4" EMT CONCRETE TIGHT D/C COUPLING
extra long description	EGS TC-612 3/4 IN EMT COMP CPLG ZNC
Long Description	Features:Concretetight, Application:Dry/Damp Location, Standard:UL 514B, CSA C22.2, NEMA FB-1, Trade Size:0.75IN, Outside Diameter:1.21IN, Length:1.78IN,Material:Zinc Die Cast
Product Type	3/4 In Emt Comp CPLG ZNC D/C
Special Features	Concretetight

### Manufacturer Information

Brand	Appleton
GTIN	00687855106127
Manufacturers Part Number	TC-612
UPC	687855106127

### Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	EMT Conduit Compression Coupling

### Trade Size

Trade Size	0.75
------------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	25
Package	250
Weight Per each	0.16

## Uses, Certifications, and Standards

Application	To join lengths of steel EMT for concretetight, dry or damp locations
standard	UL 514B, UL Listed E35001, CSA C22.2 No. 18.3 CSA Certified 208044, NEMA FB-1