

Specifications



Eaton TCF30

Eaton Bussmann series TCF fuse, Bussmann Series Class CF fuse, TCF, time-delay, dual-element current limiting cube fuse, 30 A, indicating fuse, interrupting rating of 100 kA at 300 Vdc and 300 kA at 600 Vac

General specifications

PRODUCT NAME	Eaton Bussmann series TCF fuse
CATALOG NUMBER	TCF30
UPC	051712615037
PRODUCT LENGTH/DEPTH	1.88 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	0.75 in
PRODUCT WEIGHT	0.08 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified

Electrical rating	
AMPERAGE RATING	30 A
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
INTERRUPT RATING	300 kAIC at 600 Vac 100 kAIC at 300 Vdc
VOLTAGE RATING	600 Vac, 300 Vdc

General information	
CLASS	Class CF
CONNECTION	Blade end
FUSE INDICATOR	With Indicator
SPECIAL FEATURES	Finger safe
USED WITH	TCFH30N, CCP2-3-30CF

Physical details	
COLOR	Black
FUSE TYPE	Class CF Time delay
MATERIAL	Glass filled PES
NUMBER OF ELEMENTS	Dual

Resources	
CATALOGS	Bussmann Full Line Catalog Low Voltage Branch Circuit Fuse Chapter
COMPLIANCE INFORMATION	RoHS Search Tool
MULTIMEDIA	Bussmann series Fuseology The Power of Space
TECHNICAL DATA SHEETS	Bussmann series UL Class CF CUBEFuse data sheet no. 9000

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TCF30

Eaton Bussmann series TCF fuse, Bussmann Series Class CF fuse, TCF, time-delay, dual-element current limiting cube fuse, 30 A, indicating fuse, interrupting rating of 100 kA at 300 Vdc and 300 kA at 600 Vac

General specifications

PRODUCT NAME	Eaton Bussmann series TCF fuse
CATALOG NUMBER	TCF30
UPC	051712615037
PRODUCT LENGTH/DEPTH	1.88 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	0.75 in
PRODUCT WEIGHT	0.08 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified

Electrical rating	
AMPERAGE RATING	30 A
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
INTERRUPT RATING	300 kAIC at 600 Vac 100 kAIC at 300 Vdc
VOLTAGE RATING	600 Vac, 300 Vdc

General information	
CLASS	Class CF
CONNECTION	Blade end
FUSE INDICATOR	With Indicator
SPECIAL FEATURES	Finger safe
USED WITH	TCFH30N, CCP2-3-30CF

Physical details	
COLOR	Black
FUSE TYPE	Class CF Time delay
MATERIAL	Glass filled PES
NUMBER OF ELEMENTS	Dual

Resources	
CATALOGS	Bussmann Full Line Catalog Low Voltage Branch Circuit Fuse Chapter
COMPLIANCE INFORMATION	RoHS Search Tool
MULTIMEDIA	Bussmann series Fuseology The Power of Space
TECHNICAL DATA SHEETS	Bussmann series UL Class CF CUBEFuse data sheet no. 9000

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

