


Eaton TCF50

Catalog Number: TCF50

Eaton Bussmann series TCF fuse, 50 A, 60 Hz, 50 Hz, Dual, CF, Black, Blade end, Time delay, Class CF, 10 sec at 500%, 100 kAIC at 300 Vdc, 300 kAIC at 600 V, Glass filled PES, Chassis, 35 mm DIN rail, 600 V, 300 Vdc



General specifications

| | |
|--------------------------------|----------------|
| Product Name | Catalog Number |
| Eaton Bussmann series TCF fuse | TCF50 |
| UPC | EAN |
| 051712615075 | 5027590184427 |
| Product Length/Depth | Product Height |
| 2.13 in | 1.9 in |
| Product Width | Product Weight |
| 1 in | 0.17 lb |
| Warranty | Compliances |
| Not Applicable | CE Marked |
| | RoHS Compliant |
| Certifications | |
| UL Listed | |
| CSA Certified | |

Electrical rating

Amperage Rating

50 A

Frequency rating - max

60 Hz

Frequency rating - min

50 Hz

Interrupt rating

300 kAIC at 600 Vac

100 kAIC at 300 Vdc

Response time

10 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Color

Black

Fuse type

Class CF

Time delay

Material

Glass filled PES

Number of elements

Dual

Packaging type

Standard

General information

Class

Class CF

Connection

Blade end

Fuse indicator

With Indicator

Mounting method

Chassis

35 mm DIN rail

Special features

Finger safe

Used with

TCFH60N, CCP2-3-60CF

Resources

Multimedia

[Bussmann series Fuseology](#)

[The Power of Space](#)

Specifications and datasheets

[Eaton Specification Sheet - TCF50](#)

Technical data sheets

TCF50~CUBEFUSE, TCF 50A IND

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)