



THHN250BKPCS THHN 250 STR Black PCS

Southwire Company



Catalog Number	THHN250BKPCS
Manufacturer	Southwire Company
Description	THHN Building Wire, Heat, Moisture, Gasoline and Oil Resistant; Simpull(R) Technology For Easier Pulling; Sunlight Resistant Additional Information, Commercial; Industrial Application, Black, Copper Conductor Material, 250 Kcmil Conductor Size, 215 A (60°C); 255 A (75°C); 290 A (90°C) Current Rating, PVC Insulation Material, 60 Mil Insulation Thickness, Nylon Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 37 - Strands, 694 Mil Outside Diameter, Reel; Spool Package Type, Csa C22.2 No. 75; Fede
Weight per unit	0.8500 (lbs/ft)
Product Category	THHN-T90-STR (Stranded)
Features	
Tip Size	By-the-foot
Descriptions	
Description	THHN 250 STR BLACK PCS
Manufacturer Information	
Brand	Copper
Taxonomies, Classifications, and Categories	
Category Description	BUILDING WIRE
Packaging	
Carton	1
Weight Per foot	0.85