



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## THHN4RD2500 THHN 4 STR Red 2500' *Southwire Company*



Catalog Number	THHN4RD2500
Manufacturer	Southwire Company
Description	600 Volts. Copper Conductor. Thermoplastic Insulation/Nylon Sheath, Heat, Moisture, Gasoline and Oil Resistant II. Rated THHN and THWN-2. Also Rated MTW. Simpull Technology For Easier Pulling.
Weight per unit	0.1520 (lbs/ft)
Product Category	THHN-T90-STR (Stranded)

### Features

Conductor Size	4
media	Yes
Number of Conductors	1
Voltage Rating	600

### Material, Color, and Finish

Insulation Material	PVC
Jacket Material	Nylon

### Dimensions and Weight

Length	2500
--------	------

### Descriptions

Description	THHN 4 STR RED 2500'
extra long description	SWC 20498207 THHN 4 Str Cu SIM Rd 2
Features	Southwire® SIMpull THHN copper conductors are primarily used in conduit and cable trays for services, feeders and branch circuits in commercial or industrial applications as specified in the National Electrical Code. Voltage for all applications is 600 volts. SIMpull THHN copper conductors are designed to be installed without application of a pulling lubricant.
Long Description	600 Volts. Copper Conductor. Thermoplastic Insulation/Nylon Sheath, Heat, Moisture, Gasoline and Oil Resistant II. Rated THHN and THWN-2. Also rated MTW. SIMpull Technology for Easier Pulling.
Product Type	THHN 4 STR Cu Sim RD 2500R
Special Features	No Lube



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Copper
GTIN	00032886015458
Manufacturers Part Number	20498207
UPC	032886015458

## Taxonomies, Classifications, and Categories

Category Description	BUILDING WIRE
Type	THHN-2

## Availability

minimum qty	2500
-------------	------

## Packaging

Carton	2500
Weight Per foot	0.152

## Uses, Certifications, and Standards

Application	Commerical
-------------	------------