
**PASS & SEYMOUR®**

# radiant® Paddle Switches 15A, 120/277VAC



## Dependable, high-performance solutions brought to you by Legrand.


TM870, TM873, TM874

Now part of the radiant® collection, our paddle switches offer a better fit, form and finish. The smooth paddle action combines with subtle aesthetic improvements to deliver reliable performance. ON-OFF switches conform to NEMA 430-104 requirements for kitchen disposal units. Ideal for residential, multi-dwelling, commercial office and hospitality applications.

## Features & Benefits

**Easy-access green hex head ground screw.**

**External screw-pressure-plate back and side wired.** Accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire.




**Extra-long, through-body strap** eliminates floating installations and imperfect applications.

**High-impact resistant thermoplastic construction.**

**TM870LA**


- **Part of the radiant® collection.**
- **Smooth paddle action.**
- **Push wire #14 AWG.**
- **Narrow back body leaves more room for wires in the box.**
- **Tri-drive ground, terminal and mounting screws.**
- **ON-OFF switches conform to NEC 430-104 requirements for kitchen disposal units.**
- **NAFTA-Compliant Switches are ideal for use on projects subject to the provisions of the Buy American Act.**

## Compliance

cULus Listed, UL20, Conform to NEMA WD-1 and WD-6 UL Listed, File Number E140596, Standard UL20. cULus listed. Standard CSA C22.2 No. 111. Conform to NEMA WD-1 and WD-6.

## Technical Information

| Performance | |
|---|---|
| **Electrical** | |
| Maximum Working Voltage | 277VAC |
| Maximum Current Interrupting | 15A |
| Maximum Temperature Rise | 30°C |
| **Mechanical** | |
| Terminal Identification | Terminal identification in accordance with UL20 |
| Terminal Accommodation | Back and side wire terminals accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire Push wire terminals accommodate #14 AWG |
| Product Identification | Ratings are a permanent part of the device |
| **Environmental** | |
| Flammability | UL20 minimum rating |




**TM873 LA**

| Materials | |
|---|---|
| Face | Thermoplastic |
| Back Body | Thermoplastic |
| Line Contacts | .031 Brass |
| Mounting Strap | .042 Zinc-Plated Steel |
| Tamper-Resistant Shutters | Thermoplastic |
| Terminal Screws | #8 Tri-Drive Steel (Neutral = Nickel-Plated Steel) |
| Ground Screw | #8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate |
| Mounting Screws | Steel plated |

### Warranty

1 Year

## Ordering Information

### Single Pole Switches Grounding

| Catalog Number | Rating A | Rating VAC | Color | 3rd Party Compliance UL20 | 3rd Party Compliance C22.2 111 |
|---|---|---|---|---|---|
| **TM870I** | 15 | 120/277 | Ivory | • | • |
| **TM870W** | 15 | 120/277 | White | • | • |
| **TM870** | 15 | 120/277 | Brown | • | • |
| **TM870GRY** | 15 | 120/277 | Gray | • | • |
| **TM870BK** | 15 | 120/277 | Black | • | • |
| **TM870LA** | 15 | 120/277 | Light Almond | • | • |
| **TM870NICC10** | 15 | 120/277 | Nickel | • | • |
| **TM870DBCC10** | 15 | 120/277 | Dark Bronze | • | • |
| **TM870GCC10** | 15 | 120/277 | Graphite | • | • |

### Three-Way Switches Grounding

| | | | | | |
|---|---|---|---|---|---|
| **TM873I** | 15 | 120/277 | Ivory | • | • |
| **TM873W** | 15 | 120/277 | White | • | • |
| **TM873** | 15 | 120/277 | Brown | • | • |
| **TM873GRY** | 15 | 120/277 | Gray | • | • |
| **TM873BK** | 15 | 120/277 | Black | • | • |
| **TM873LA** | 15 | 120/277 | Light Almond | • | • |
| **TM873NICC10** | 15 | 120/277 | Nickel | • | • |
| **TM873DBCC10** | 15 | 120/277 | Dark Bronze | • | • |
| **TM873GCC10** | 15 | 120/277 | Graphite | • | • |

### Four-Way Switches Grounding

| | | | | | |
|---|---|---|---|---|---|
| **TM874I** | 15 | 120/277 | Ivory | • | • |
| **TM874W** | 15 | 120/277 | White | • | • |
| **TM874** | 15 | 120/277 | Brown | • | • |
| **TM874BK** | 15 | 120/277 | Black | • | • |
| **TM874LA** | 15 | 120/277 | Light Almond | • | • |
| **TM874NICC6** | 15 | 120/277 | Nickel | • | • |
| **TM874DBCC6** | 15 | 120/277 | Dark Bronze | • | • |
| **TM874GCC6** | 15 | 120/277 | Graphite | • | • |

## Vertical Markets

- Office
- Residential
- Multiple Dwelling
- Hospitality/Lodging

## Also available in the radiant® collection

- GFCI Receptacles
- Standard & Tamper-Resistant Receptacles
- Lighting & Fan Controls
- Timers
- Combination Devices
- USB Charging Devices
- Night Lights
- Screwless Wall Plates
- Sensors
- Home Automation Controls

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

**Legrand, North America**
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us


570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

**SF20190 June 2025 ©2025 Legrand All Rights Reserved**

**PASS & SEYMOUR®**

# radiant® Paddle Switches 15A, 120/277VAC



## Dependable, high-performance solutions brought to you by Legrand.


TM870, TM873, TM874

Now part of the radiant® collection, our paddle switches offer a better fit, form and finish. The smooth paddle action combines with subtle aesthetic improvements to deliver reliable performance. ON-OFF switches conform to NEMA 430-104 requirements for kitchen disposal units. Ideal for residential, multi-dwelling, commercial office and hospitality applications.

## Features & Benefits

**Easy-access green hex head ground screw.**

**External screw-pressure-plate back and side wired.** Accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire.




**Extra-long, through-body strap** eliminates floating installations and imperfect applications.

**High-impact resistant thermoplastic construction.**

**TM870LA**


- **Part of the radiant® collection.**
- **Smooth paddle action.**
- **Push wire #14 AWG.**
- **Narrow back body leaves more room for wires in the box.**
- **Tri-drive ground, terminal and mounting screws.**
- **ON-OFF switches conform to NEC 430-104 requirements for kitchen disposal units.**
- **NAFTA-Compliant Switches are ideal for use on projects subject to the provisions of the Buy American Act.**

## Compliance

cULus Listed, UL20, Conform to NEMA WD-1 and WD-6 UL Listed, File Number E140596, Standard UL20. cULus listed. Standard CSA C22.2 No. 111. Conform to NEMA WD-1 and WD-6.

## Technical Information

| Performance | |
|---|---|
| **Electrical** | |
| Maximum Working Voltage | 277VAC |
| Maximum Current Interrupting | 15A |
| Maximum Temperature Rise | 30°C |
| **Mechanical** | |
| Terminal Identification | Terminal identification in accordance with UL20 |
| Terminal Accommodation | Back and side wire terminals accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire Push wire terminals accommodate #14 AWG |
| Product Identification | Ratings are a permanent part of the device |
| **Environmental** | |
| Flammability | UL20 minimum rating |




**TM873 LA**

| Materials | |
|---|---|
| Face | Thermoplastic |
| Back Body | Thermoplastic |
| Line Contacts | .031 Brass |
| Mounting Strap | .042 Zinc-Plated Steel |
| Tamper-Resistant Shutters | Thermoplastic |
| Terminal Screws | #8 Tri-Drive Steel (Neutral = Nickel-Plated Steel) |
| Ground Screw | #8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate |
| Mounting Screws | Steel plated |

### Warranty

1 Year

## Ordering Information

### Single Pole Switches Grounding

| Catalog Number | Rating A | Rating VAC | Color | 3rd Party Compliance UL20 | 3rd Party Compliance C22.2 111 |
|---|---|---|---|---|---|
| **TM870I** | 15 | 120/277 | Ivory | • | • |
| **TM870W** | 15 | 120/277 | White | • | • |
| **TM870** | 15 | 120/277 | Brown | • | • |
| **TM870GRY** | 15 | 120/277 | Gray | • | • |
| **TM870BK** | 15 | 120/277 | Black | • | • |
| **TM870LA** | 15 | 120/277 | Light Almond | • | • |
| **TM870NICC10** | 15 | 120/277 | Nickel | • | • |
| **TM870DBCC10** | 15 | 120/277 | Dark Bronze | • | • |
| **TM870GCC10** | 15 | 120/277 | Graphite | • | • |

### Three-Way Switches Grounding

| | | | | | |
|---|---|---|---|---|---|
| **TM873I** | 15 | 120/277 | Ivory | • | • |
| **TM873W** | 15 | 120/277 | White | • | • |
| **TM873** | 15 | 120/277 | Brown | • | • |
| **TM873GRY** | 15 | 120/277 | Gray | • | • |
| **TM873BK** | 15 | 120/277 | Black | • | • |
| **TM873LA** | 15 | 120/277 | Light Almond | • | • |
| **TM873NICC10** | 15 | 120/277 | Nickel | • | • |
| **TM873DBCC10** | 15 | 120/277 | Dark Bronze | • | • |
| **TM873GCC10** | 15 | 120/277 | Graphite | • | • |

### Four-Way Switches Grounding

| | | | | | |
|---|---|---|---|---|---|
| **TM874I** | 15 | 120/277 | Ivory | • | • |
| **TM874W** | 15 | 120/277 | White | • | • |
| **TM874** | 15 | 120/277 | Brown | • | • |
| **TM874BK** | 15 | 120/277 | Black | • | • |
| **TM874LA** | 15 | 120/277 | Light Almond | • | • |
| **TM874NICC6** | 15 | 120/277 | Nickel | • | • |
| **TM874DBCC6** | 15 | 120/277 | Dark Bronze | • | • |
| **TM874GCC6** | 15 | 120/277 | Graphite | • | • |

## Vertical Markets

- Office
- Residential
- Multiple Dwelling
- Hospitality/Lodging

## Also available in the radiant® collection

- GFCI Receptacles
- Standard & Tamper-Resistant Receptacles
- Lighting & Fan Controls
- Timers
- Combination Devices
- USB Charging Devices
- Night Lights
- Screwless Wall Plates
- Sensors
- Home Automation Controls

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

**Legrand, North America**
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

**SF20190 June 2025 ©2025 Legrand All Rights Reserved**