

# Straight Blade Receptacles TradeMaster® Decorator Hallway Lights & Combination Devices




Pass & Seymour




Straight Blade Receptacles


Features	
<ul style="list-style-type: none"> <li>Impact-resistant face and body.</li> <li>GE Lexan™ high impact-resistant lens.</li> <li>External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.</li> <li>Ground screw position under the end of the strap minimizes the risk of contact.</li> <li>Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.</li> <li>Sensor automatically turns light ON in the dark.</li> </ul>	<ul style="list-style-type: none"> <li>Increased light output for better illumination.</li> <li>Light sensor for enhanced sensitivity.</li> </ul> <p><b>Tamper-Resistant Combination Version:</b></p> <ul style="list-style-type: none"> <li>UL tested shutter mechanism for protection against improper object insertion per UL478.</li> <li>Specially designed for increased protection of children in their homes.</li> <li>Superior protection than traditional outlet “caps” or “protection plates.”</li> </ul>




TMHWLCC



TMHWLECC



TM8HWLWCC



TM8HWLTRLACC

Hallway Lights & Combination Devices

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	3rd Party Compliance
				UL1598
<b>TradeMaster® Decorator Full Hallway Light with Light Sensor</b>				
TMHWLCC	— 120	0.1328	Clear	•
<b>Enhanced Decorator Full Hallway Light with Light Sensor</b>				
TMHWLECC	— 120	1.079	Clear	•
<b>Enhanced Decorator Full Hallway Light without Light Sensor</b>				
TMHWLENSCC	— 120	1.113	Clear	•
<b>Full Hallway Decorator Light for use with P&amp;S Metal Louver Plates**</b>				
TMHWLLOUVCC	— 120	0.0843	Clear	•

\*FCD = Foot Candle Distance, 1 Lumen = 1 FCD. See page S-56 for more information.

\*\*For Louver Plates, see Page Q-21.

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance
					UL498
<b>TradeMaster® Decorator Hallway Light &amp; Single Receptacle</b>					
TM8HWLICC	15 120/125	0.1442	Ivory	5-15R	•
TM8HWLWCC	15 120/125	0.1442	White	5-15R	•
TM8HWLCC	15 120/125	0.1442	Brown	5-15R	•
TM8HWLBKCC	15 120/125	0.1442	Black	5-15R	•
TM8HWLLACC	15 120/125	0.1442	Light Almond	5-15R	•
<b>Decorator Hallway Light with High Output Light &amp; Tamper-Resistant Single Receptacle</b>					
TM8HWLTRICC	15 125	0.2561	Ivory	5-15R	•
TM8HWLTRWCC	15 125	0.2561	White	5-15R	•
TM8HWLTRCC	15 125	0.2561	Brown	5-15R	•
TM8HWLTRBKCC	15 125	0.2561	Black	5-15R	•
TM8HWLTRLACC	15 125	0.2561	Light Almond	5-15R	•

\*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See page S-56 for more information.

For complete line of Decorator Combination Devices, see Pages D-9 – D-12, D-20, D-24, D-33 and D-39.

All devices listed on this page conform to NEMA WD-1 and WD-6.

# Devices & Wall Plates Color Selection Chart



Pass & Seymour

## Devices & Plastic Wall Plate Colors

Ivory	Light Almond	White	Green		
Black	Blue	Brown	Gray	Orange	Red

See specific device and wall plate catalog charts for particular color availabilities.

## Metal Wall Plates

<b>Metal Finish</b> Aluminum	Brass (Brushed)	Polished Brass	Stainless Steel	Brushed Bronze	Chrome

## Custom Metal Wall Plates Paint Finish Colors

<b>Paint Color</b> Orange	Green	Gray	Yellow	Glossy Black	Brown	White
<b>Paint Color</b> Primer	Red	Pink	Flat Black	Ivory	Light Almond	Blue

To order custom metal wall plates, see Pages Q-43 – Q-45.

For additional colors consult factory.

# Straight Blade Receptacles TradeMaster® Decorator Hallway Lights & Combination Devices




Pass & Seymour




Straight Blade Receptacles


Features	
<ul style="list-style-type: none"> <li>Impact-resistant face and body.</li> <li>GE Lexan™ high impact-resistant lens.</li> <li>External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.</li> <li>Ground screw position under the end of the strap minimizes the risk of contact.</li> <li>Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.</li> <li>Sensor automatically turns light ON in the dark.</li> </ul>	<ul style="list-style-type: none"> <li>Increased light output for better illumination.</li> <li>Light sensor for enhanced sensitivity.</li> </ul> <p><b>Tamper-Resistant Combination Version:</b></p> <ul style="list-style-type: none"> <li>UL tested shutter mechanism for protection against improper object insertion per UL478.</li> <li>Specially designed for increased protection of children in their homes.</li> <li>Superior protection than traditional outlet “caps” or “protection plates.”</li> </ul>




TMHWLCC



TMHWLECC



TM8HWLWCC



TM8HWLTRLACC

Hallway Lights & Combination Devices

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	3rd Party Compliance	
				UL	UL1598
<b>TradeMaster® Decorator Full Hallway Light with Light Sensor</b>					
TMHWLCC	— 120	0.1328	Clear		•
<b>Enhanced Decorator Full Hallway Light with Light Sensor</b>					
TMHWLECC	— 120	1.079	Clear		•
<b>Enhanced Decorator Full Hallway Light without Light Sensor</b>					
TMHWLENSCC	— 120	1.113	Clear		•
<b>Full Hallway Decorator Light for use with P&amp;S Metal Louver Plates**</b>					
TMHWLLOUVCC	— 120	0.0843	Clear		•

\*FCD = Foot Candle Distance, 1 Lumen = 1 FCD. See page S-56 for more information.

\*\*For Louver Plates, see Page Q-21.

Catalog Number	Rating A. VAC	Light Output In 1' FCD*	Color	NEMA Config. No.	3rd Party Compliance	
					UL	UL498
<b>TradeMaster® Decorator Hallway Light &amp; Single Receptacle</b>						
TM8HWLICC	15 120/125	0.1442	Ivory	5-15R		•
TM8HWLWCC	15 120/125	0.1442	White	5-15R		•
TM8HWLCC	15 120/125	0.1442	Brown	5-15R		•
TM8HWLBKCC	15 120/125	0.1442	Black	5-15R		•
TM8HWLLACC	15 120/125	0.1442	Light Almond	5-15R		•
<b>Decorator Hallway Light with High Output Light &amp; Tamper-Resistant Single Receptacle</b>						
TM8HWLTRICC	15 125	0.2561	Ivory	5-15R		•
TM8HWLTRWCC	15 125	0.2561	White	5-15R		•
TM8HWLTRCC	15 125	0.2561	Brown	5-15R		•
TM8HWLTRBKCC	15 125	0.2561	Black	5-15R		•
TM8HWLTRLACC	15 125	0.2561	Light Almond	5-15R		•

\*FCD = Foot Candle Distance. 1 Lumen = 1 FCD. See page S-56 for more information.

For complete line of Decorator Combination Devices, see Pages D-9 – D-12, D-20, D-24, D-33 and D-39.

All devices listed on this page conform to NEMA WD-1 and WD-6.

# Devices & Wall Plates Color Selection Chart



Pass & Seymour

## Devices & Plastic Wall Plate Colors

Ivory	Light Almond	White	Green		
Black	Blue	Brown	Gray	Orange	Red

See specific device and wall plate catalog charts for particular color availabilities.

## Metal Wall Plates

<b>Metal Finish</b> Aluminum	Brass (Brushed)	Polished Brass	Stainless Steel	Brushed Bronze	Chrome

## Custom Metal Wall Plates Paint Finish Colors

<b>Paint Color</b> Orange	Green	Gray	Yellow	Glossy Black	Brown	White
<b>Paint Color</b> Primer	Red	Pink	Flat Black	Ivory	Light Almond	Blue

To order custom metal wall plates, see Pages Q-43 – Q-45.

For additional colors consult factory.