



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMCX4140 1-1/4" Cord Grips

Crouse-Hinds

Catalog Number	TMCX4140
Manufacturer	Crouse-Hinds
Description	TMC Armored Cable Gland, Aluminum, 1-1/4 In Size, 3.125 In (Gland) Length, -25 °C Operating Temperature, +60 °C Operating Temperature, Grip Connection, Non-Insulated, 1.08 LB/Ea
Weight per unit	1.1 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

connection	Male NPT
dimensions	4.1000 IN X 2.4400 IN X 2.4400 IN

Material, Color, and Finish

Finish	Nickel Plated
--------	---------------

Descriptions

Description	1-1/4" CORD GRIPS
extra long description	CRS-H TMCX4140 1 1/4 FT MC CAB ARMO
Features	For use with metal-clad, non-armoured and tray cable, TMCX cable fittings are installed to provide a means for terminating cable at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution. They are used to form a mechanical watertight connection and to provide ground continuity of cable armour. Applied in Division 1 locations and when a seal is required.

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274414690
UPC	782274414690

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland

Packaging

Carton	1
Weight Per each	1.075

Uses, Certifications, and Standards

Enclosure standard	IP56, Class I Div 1 Group A B C D, Class II, Class III
Temperature Rating	UL (CANADA AND US), CUL
	-25 To 60 Deg C