

Specifications



Eaton TP114

Eaton Crouse-Hinds series Non-Gangable Switch Box, (1) 1/2", Conduit (no clamps), 1-1/2", (1) 1/2", Steel, Ears, Non-gangable, 7.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series non-gangable switch box
CATALOG NUMBER	TP114
UPC	786189101140
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	0.39 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	1-1/2"
TYPE	Non-gangable
CAPACITY	7.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)

END KNOCKOUTS	(1) 1/2 in
BOTTOM KNOCKOUTS	(1) 1/2 in
MATERIAL	Steel
SPECIAL FEATURES	Ears

Resources

CATALOGS

[Crouse-Hinds series Steel Switch Boxes catalog page](#)

CERTIFICATION REPORTS

[Steel Switch Boxes Canadian certification](#)

[Steel Switch Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP114](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

