

Specifications



Eaton TP238

Eaton Crouse-Hinds series Switch Box, (1) 1/2", 2, NM clamps, 3-1/2", (1) 1/2" , Steel, (2) 1/2", Ears, Gangable, 18.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series switch box
CATALOG NUMBER	TP238
UPC	786189102383
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.8 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	3-1/2"
TYPE	Gangable
CAPACITY	18 cubic in
CONDUIT/CABLE	NM clamps

END KNOCKOUTS	(1) 1/2 in
SIDE KNOCKOUTS	(2) 1/2 in
BOTTOM KNOCKOUTS	(1) 1/2 in
CABLE KNOCKOUTS	2
MATERIAL	Steel
SPECIAL FEATURES	Ears

Resources

CATALOGS [Crouse-Hinds series Steel Switch Boxes catalog page](#)

CERTIFICATION REPORTS [Steel Switch Boxes UL certification](#)

[Steel Switch Boxes Canadian certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP238](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

