

Eaton TP318

Catalog Number: TP318

Eaton Crouse-Hinds series Octagon Outlet Box, (1) 1/2", 4", C, 4, NM clamps, 2-1/8", Steel, (2) 1/2", Fixture rated, 21.5 cubic inch capacity

General specifications



| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series octagon outlet box | TP318 |
| | UPC |
| | 786189103182 |
| Product Length/Depth | Product Height |
| 4 in | 2.13 in |
| Product Width | Product Weight |
| 4 in | 0.88 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4"

Depth

2-1/8"

Capacity

21.5 cubic in

Conduit/cable

NM clamps

Bracket style

C

Cable knockouts

4

Side knockouts

(2) 1/2 in

Bottom Knockouts

(1) 1/2 in

Material

Steel

Special features

Fixture rated

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP318](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)