

Specifications



Photo is representative

Eaton TP432PF

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Conduit (no clamps), Welded, 2-1/8", Steel, (8) 3/4", Includes ground screw with pigtail lead, 30.3 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP432PF
UPC	662279000916
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.93 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
---------------------	------------------------

Product specifications

BOX SIZE	4"
----------	----

	Locations
STANDARDS TYPE	NEC/CEC

CAPACITY	30.3 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)
CONSTRUCTION	Welded
SIDE KNOCKOUTS	(8) 3/4 in
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
MATERIAL	Steel
SPECIAL FEATURES	Includes ground screw with pigtail lead

Resources

CATALOGS

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP432PF](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.



Specifications



Photo is representative

Eaton TP432PF

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Conduit (no clamps), Welded, 2-1/8", Steel, (8) 3/4", Includes ground screw with pigtail lead, 30.3 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP432PF
UPC	662279000916
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.93 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
---------------------	------------------------

Product specifications

BOX SIZE	4"
----------	----

	Locations
STANDARDS TYPE	NEC/CEC

CAPACITY	30.3 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)
CONSTRUCTION	Welded
SIDE KNOCKOUTS	(8) 3/4 in
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
MATERIAL	Steel
SPECIAL FEATURES	Includes ground screw with pigtail lead

Resources

CATALOGS

[Crouse-Hinds series 4-Inch
Steel Square Boxes and Covers
catalog page](#)

CERTIFICATION REPORTS

[4-Inch Steel Square Outlet
Boxes, Covers, Extension
Rings UL certification](#)

[4-Inch Steel Square Outlet
Boxes, Covers, Extension
Rings Canadian certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -
TP432PF](#)

[Steel Outlet Boxes for
Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.

