



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR20 Duplex Recp TR 20A 125V BN

*Pass & Seymour/Legrand*

Catalog Number	TR20
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Commercial Grade Receptacle, 20A, 125V. Available In 6 Colors. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page.
Weight per unit	0.2478 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Side wire
Dielectric Strength	Withstands 1500V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Mounting Type	Box
Number of Wires	3
Outlet Type	Tamper-Resistant
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Height	3.281
Width	1.130



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	DUPLEX RECP TR 20A 125V BN
extra long description	P&S TR20 RECEP DUP TAMPER RESIS 20A
Features	Single Piece Plated Steel Mounting Strap
Long Description	Tamper-Resistant Commercial Grade Receptacle, 20A, 125V. Available in 6 colors. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.
Product Type	Recep Dup Tamper Resis 20A/125V BN
Special Features	Dual mechanical shutter system to help prevent insertion of foreign objects. Auto-ground clip assures positive ground. Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. Backed-out tri-drive steel terminal screws for faster installation. Side wire capability. Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly. .032 inch thick brass triple-wipe power contacts. Two drive screws anchor steel st

## Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007241631
Manufacturers Part Number	TR20
UPC	785007241631

## Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.2478

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Frequency Rating	60 Hz
Mounting	WALL
nema rating	5-20R
Operating Temperature	-40°-60°C
standard	CULUS, cULus UL498, CSA C22.2 No. 42