

Specifications



Photo is representative

Eaton TR5262WS-SP-L

Eaton TVSS receptacle, LED indicat and alarm, #14 - #10 AWG, 15A, Comm specif, Wall/flush mnt, Bk and sd wire, 840J, 2 recept, -40° to 60°C, Wht, Brs, Strght blade, Hi-impct resist thermpls/nylon, 5-15R, Dplx 756832 756832

General specifications

PRODUCT NAME	Eaton TVSS receptacle
CATALOG NUMBER	TR5262WS-SP-L
UPC	032664756832
PRODUCT LENGTH/DEPTH	1.62 in
PRODUCT HEIGHT	4.2 in
PRODUCT WIDTH	1.7 in
PRODUCT WEIGHT	0.28 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	TVSS receptacle



Powering Business Worldwide

Product specifications

DEVICE TYPE	Straight blade
SPECIAL FEATURES	LED indicators & alarm
TYPE	TVSS surge protection receptacle
AMPERAGE RATING	15A
VOLTAGE RATING	125 V
CONTACT MATERIAL	Brass
JOULES	560J
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10-14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-15R
APPLICATION	Commercial
DEVICE GRADE	Commercial
WIRING METHOD	Back and side
MATERIAL	Thermoplastic
NUMBER OF RECEPTACLES	2
OPERATING TEMPERATURE	-40 to 60 °C
TORQUE RATING	14 lbf-inch
NUMBER OF WIRES	3
MOUNTING METHOD	Flush Wall
NUMBER OF POLES	Two-pole
STYLE TYPE	Duplex
COLOR	White
FACE/BODY MATERIAL	High-impact resistant thermoplastic Nylon
RECEPTACLE TYPE	Two-pole, three-wire, grounding

Resources

CROSS REFERENCES	TR surge receptacles cross reference guide
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TR5262WS-SP-L TR surge protection receptacles w/audible alarm and LED indicators spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

