



TAMPER-RESISTANT CONSTRUCTION SPEC GRADE SINGLE RECEPTACLES, BACK & SIDE WIRE, 20A, 125V, IVORY

TR53511 | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Construction Spec Grade Single Receptacle Back & Side Wire 20amp 125volt Ivory

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Type: Single Receptacles
Number Of Poles: 2
Number Of Wires: 3
Special Features: Tamper-Resistant,back,side wire

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
Federal Spec: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406
UR: No

DIMENSIONS

Depth (US): 1.19"
Height (US): 3.28"
Width (US): 1.296"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 5-20R
Volts: 125V
Volts (AC): 125
Capacity: Single
Grade Type: Construction

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant





TAMPER-RESISTANT CONSTRUCTION SPEC GRADE SINGLE RECEPTACLES, BACK & SIDE WIRE, 20A, 125V, IVORY

TR53511 | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Construction Spec Grade Single Receptacle Back & Side Wire 20amp 125volt Ivory

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory

Type: Single Receptacles

Number Of Poles: 2

Number Of Wires: 3

Special Features: Tamper-Resistant,back,side wire

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

UR: No

DIMENSIONS

Depth (US): 1.19"
Height (US): 3.28"
Width (US): 1.296"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 5-20R
Volts: 125V
Volts (AC): 125
Capacity: Single
Grade Type: Construction

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

