




Ty-Duct™



NOTES:

1. MATERIAL: RIGID PVC
2. TEMPERATURE RATING: -40°F [-40°C] TO 122°F [50°C]
3. FLAMMABILITY RATING: UL94V-0
4. NORTH AMERICAN AND DIN STYLE MOUNTING HOLES
5. FLUSH MOUNT COVER DESIGN. COVER MOUNTS FLUSH WITH SIDE WALLS

GENERAL NOTES

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

- | | |
|---|--|
| 2 | SEE ERN 2006994 FOR APPROVAL SIGNATURES & RELEASE DATE.
PROJECT NO: FD55400 |
|---|--|

DESCRIPTION:

WIDE SLOT WIRING DUCT

ORIGINAL PROJECT NO / (ERN NO)

FD55400 / (2005724)

SHEET NO:

1 OF 6


REV. NO:

2

DRAWING NO:

WSD-000180

Thomas & Betts
www.tnb.com



CATALOG NO.	A (WIDTH)	B (HEIGHT)	C	D	COVER CATALOG NO.
TY75X1WP*6	.940 [23,88]	1.025 [26,04]	.430 [10,92]	.800 [20,32]	TY75CP*6
TY75X15WP*6		1.500 [38,1]	.830 [21,08]		
TY75X2WP*6		2.014 [51,16]	1.249 [31,72]		
TY1X1WP*6	1.250 [31,75]	1.025 [26,04]	.430 [10,92]	1.000 [25,4]	TY1CP*6
TY1X15WP*6		1.500 [38,1]	.830 [21,08]		
TY1X2WP*6		2.014 [51,16]	1.249 [31,72]		
TY1X3WP*6		3.000 [76,2]	2.175 [55,25]		
TY1X4WP*6		4.317 [109,65]	3.487 [88,57]		

* = COLOR CODE

B = BLACK G = GRAY I = INTRINSIC BLUE W = WHITE

Thomas & Betts
www.tnb.com

DESCRIPTION:

WIDE SLOT WIRING DUCT

SHEET NO:


2 OF 6

REV. NO:

2

DRAWING NO:

WSD-000180



CATALOG NO.	B (HEIGHT)	C	D	F	COVER CATALOG NO.
TY15X1WP*6	1.025 [26,04]	.430 [10,92]	.800 [20,32]	.300 [7,62]	TY15CP*6
TY15X15WP*6	1.500 [38,1]	.830 [21,08]			
TY15X2WP*6	2.014 [51,16]	1.249 [31,72]			
TY15X3WP*6	3.000 [76,2]	2.175 [55,25]	1.000 [25,4]		
TY15X4WP*6	4.317 [109,65]	3.487 [88,57]			

* = COLOR CODE

B = BLACK G = GRAY I = INTRINSIC BLUE W = WHITE

Thomas & Betts
www.tnb.com

DESCRIPTION:

WIDE SLOT WIRING DUCT

SHEET NO:


3 OF 6

REV. NO:

2

DRAWING NO:

WSD-000180



CATALOG NO.	A (WIDTH)	B (HEIGHT)	C	D	F	COVER CATALOG NO.
TY2X1WP*6	2.250 [57,15]	1.046 [26,57]	.430 [10,92]	.800 [20,32]	.300 [7,62]	TY2CP*6
TY2X15WP*6		1.521 [38,63]	.830 [21,08]			
TY2X2WP*6		2.034 [51,66]	1.249 [31,72]			
TY2X3WP*6		3.000 [76,2]	2.175 [55,25]	1.000 [25,4]		
TY2X4WP*6		4.332 [110,03]	3.487 [88,57]			
TY2X5WP*6		5.020 [127,51]	4.161 [105,69]			
TY25X2WP*6	2.750 [69,85]	2.034 [51,66]	1.249 [31,72]	.800 [20,32]	.300 [7,62]	TY25CP*6
TY25X3WP*6		3.000 [76,2]	2.175 [55,25]	1.000 [25,4]		
TY25X4WP*6		4.332 [110,03]	3.487 [88,57]			

* = COLOR CODE

B = BLACK G = GRAY I = INTRINSIC BLUE W = WHITE

Thomas & Betts
www.tnb.com

DESCRIPTION:

WIDE SLOT WIRING DUCT

SHEET NO:


4 OF 6

REV. NO:

2

DRAWING NO:

WSD-000180



CATALOG NO.	A (WIDTH)	B (HEIGHT)	C	D	F	COVER CATALOG NO.
TY3X1WP*6	3.250 [82,55]	1.055 [26,8]	.430 [10,92]	.800 [20,32]	.300 [7,62]	TY3CP*6
TY3X2WP*6		2.081 [52,86]	1.249 [31,72]			
TY3X3WP*6		3.056 [77,62]	2.175 [55,25]	1.000 [25,4]		
TY3X4WP*6		4.387 [111,43]	3.487 [88,57]			
TY3X5WP*6		5.061 [128,55]	4.161 [105,69]	1.333 [33,86]		
TY4X15WP*6	4.250 [107,95]	1.567 [39,8]	.830 [21,08]	.800 [20,32]	.300 [7,62]	TY4CP*6
TY4X2WP*6		2.081 [52,86]	1.249 [31,72]			
TY4X3WP*6		3.056 [77,62]	2.175 [55,25]	1.000 [25,4]		
TY4X4WP*6		4.387 [111,43]	3.487 [88,57]			
TY4X5WP*6		5.061 [128,55]	4.161 [105,69]	1.333 [33,86]		
TY6X4WP*6	6.250 [158,75]	4.387 [111,43]	3.487 [88,57]	.800 [20,32]	.300 [7,62]	TY6CP*6

* = COLOR CODE

B = BLACK G = GRAY I = INTRINSIC BLUE W = WHITE

Thomas & Betts
www.tnb.com

DESCRIPTION:

WIDE SLOT WIRING DUCT

SHEET NO:

5 OF 6

REV. NO:

2

DRAWING NO:

WSD-000180

NOMINAL DUCT SIZE W H		AREA SQUARE	ELECTRICAL												DATA CABLE																
			8 AWG		10 AWG		12 AWG		14 AWG		16 AWG		18 AWG		22 AWG		24 AWG														
			Ø.216	THHN	Ø.153	THHN	Ø.122	THHN	MTW	Ø.158	Ø.105	THHN	MTW	Ø.139	Ø.165	THHN	MTW	Ø.096	Ø.125	THHN	MTW	Ø.084	THHN	MTW	Ø.065	Ø.217	UTP/CM CAT5E	Ø.250	UTP/CM CAT6	Ø.422	UTP/CM
.75 x 1.00		.750	5	9	14	9			19	11	8	23	14		30	17	51	5	3	1											
.75 x 1.50		1.125	7	14	22	13			29	17	12	35	21		46	25	76	7	5	2											
.75 x 2.00		1.500	9	18	29	17			39	22	16	47	27		61	34	101	9	7	2											
1.00 x 1.00		1.000	6	12	19	11			26	15	10	31	18		40	22	68	6	5	2											
1.00 x 1.50		1.500	9	18	29	17			39	22	16	47	27		61	34	101	9	7	2											
1.00 x 2.00		2.000	12	24	38	23			52	30	21	62	37		81	45	135	12	9	3											
1.00 x 3.00		3.000	18	37	58	34			78	44	31	93	55		121	67	203	18	14	5											
1.00 x 4.00		4.000	24	49	77	46			104	59	42	124	73		162	90	270	24	18	6											
1.50 x 1.00		1.500	9	18	29	17			39	22	16	47	27		61	34	101	9	7	2											
1.50 x 1.50		2.250	14	27	43	26			58	33	24	70	41		91	50	152	14	10	4											
1.50 x 2.00		3.000	18	37	58	34			78	44	31	93	55		121	67	203	18	14	5											
1.50 x 3.00		4.500	28	55	86	52			117	67	47	140	82		182	101	304	27	21	7											
1.50 x 4.00		6.000	37	73	115	69			155	89	63	186	110		243	134	406	36	27	10											
2.00 x 1.00		2.000	12	24	38	23			52	30	21	62	37		81	45	135	12	9	3											
2.00 x 1.50		3.000	18	37	58	34			78	44	31	93	55		121	67	203	18	14	5											
2.00 x 2.00		4.000	24	49	77	46			104	59	42	124	73		162	90	270	24	18	6											
2.00 x 3.00		6.000	37	73	115	69			155	89	63	186	110		243	134	406	36	27	10											
2.00 x 4.00		8.000	49	98	154	92			207	118	84	248	146		324	179	541	49	37	13											
2.00 x 5.00		10.000	61	122	192	114			259	148	105	310	183		405	224	676	61	46	16											
2.50 x 2.00		5.000	31	61	96	57			130	74	52	155	91		202	112	338	30	23	8											
2.50 x 3.00		7.500	46	92	144	86			194	111	79	233	137		304	168	507	46	34	12											
2.50 x 4.00		10.000	61	122	192	114			259	148	105	310	183		405	224	676	61	46	16											
3.00 x 1.00		3.000	18	37	58	34			78	44	31	93	55		121	67	203	18	14	5											
3.00 x 2.00		6.000	37	73	115	69			155	89	63	186	110		243	134	406	36	27	10											
3.00 x 3.00		9.000	55	110	173	103			233	133	94	279	165		364	201	609	55	41	14											
3.00 x 4.00		12.000	73	146	230	137			311	177	126	372	219		486	269	811	73	55	19											
3.00 x 5.00		15.000	92	183	288	172			389	222	157	465	274		607	336	1014	91	69	24											
4.00 x 1.50		6.000	37	73	115	69			155	89	63	186	110		243	134	406	36	27	10											
4.00 x 2.00		8.000	49	98	154	92			207	118	84	248	146		324	179	541	49	37	13											
4.00 x 3.00		12.000	73	146	230	137			311	177	126	372	219		486	269	811	73	55	19											
4.00 x 4.00		16.000	98	195	307	183			415	237	168	496	293		648	358	1082	97	73	26											
4.00 x 5.00		20.000	122	244	384	229			518	296	210	620	366		810	448	1352	121	91	32											
6.00 x 4.00		24.000	147	293	461	275			622	355	252	744	439		972	537	1623	146	110	39											
			NOTE: WIRE FILL IS BASED ON 50% FILL OF DUCT AREA																												

Thomas & Betts www.tnb.com				DESCRIPTION:		
				WIDE SLOT WIRING DUCT		
		SHEET NO: 6 OF 6	REV. NO: 2	DRAWING NO: WSD-000180		

Thomas & Betts
www.tnb.com

DESCRIPTION:

WIDE SLOT WIRING DUCT

SHEET NO:

6 OF 6

REV. NO:


2

DRAWING NO:

WSD-000180



Ty-Duct™



NOTES:

1. MATERIAL: RIGID PVC
2. TEMPERATURE RATING: -40°F [-40°C] TO 122°F [50°C]
3. FLAMMABILITY RATING: UL94V-0
4. NORTH AMERICAN AND DIN STYLE MOUNTING HOLES
5. FLUSH MOUNT COVER DESIGN. COVER MOUNTS FLUSH WITH SIDE WALLS

GENERAL NOTES

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

- | | |
|---|--|
| 2 | SEE ERN 2006994 FOR APPROVAL SIGNATURES & RELEASE DATE.
PROJECT NO: FD55400 |
|---|--|

DESCRIPTION:

WIDE SLOT WIRING DUCT

ORIGINAL PROJECT NO / (ERN NO)

FD55400 / (2005724)

SHEET NO:

1 OF 6


REV. NO:

2

DRAWING NO:

WSD-000180

Thomas & Betts
www.tnb.com



CATALOG NO.	A (WIDTH)	B (HEIGHT)	C	D	COVER CATALOG NO.
TY75X1WP*6	.940 [23,88]	1.025 [26,04]	.430 [10,92]	.800 [20,32]	TY75CP*6
TY75X15WP*6		1.500 [38,1]	.830 [21,08]		
TY75X2WP*6		2.014 [51,16]	1.249 [31,72]		
TY1X1WP*6	1.250 [31,75]	1.025 [26,04]	.430 [10,92]	1.000 [25,4]	TY1CP*6
TY1X15WP*6		1.500 [38,1]	.830 [21,08]		
TY1X2WP*6		2.014 [51,16]	1.249 [31,72]		
TY1X3WP*6		3.000 [76,2]	2.175 [55,25]		
TY1X4WP*6		4.317 [109,65]	3.487 [88,57]		

* = COLOR CODE

B = BLACK G = GRAY I = INTRINSIC BLUE W = WHITE

Thomas & Betts
www.tnb.com

DESCRIPTION:

WIDE SLOT WIRING DUCT

SHEET NO:


2 OF 6

REV. NO:

2

DRAWING NO:

WSD-000180



CATALOG NO.	B (HEIGHT)	C	D	F	COVER CATALOG NO.
TY15X1WP*6	1.025 [26,04]	.430 [10,92]	.800 [20,32]	.300 [7,62]	TY15CP*6
TY15X15WP*6	1.500 [38,1]	.830 [21,08]			
TY15X2WP*6	2.014 [51,16]	1.249 [31,72]			
TY15X3WP*6	3.000 [76,2]	2.175 [55,25]	1.000 [25,4]		
TY15X4WP*6	4.317 [109,65]	3.487 [88,57]			

* = COLOR CODE

B = BLACK G = GRAY I = INTRINSIC BLUE W = WHITE

Thomas & Betts
www.tnb.com

DESCRIPTION:

WIDE SLOT WIRING DUCT

SHEET NO:


3 OF 6

REV. NO:

2

DRAWING NO:

WSD-000180



CATALOG NO.	A (WIDTH)	B (HEIGHT)	C	D	F	COVER CATALOG NO.
TY2X1WP*6	2.250 [57,15]	1.046 [26,57]	.430 [10,92]	.800 [20,32]	.300 [7,62]	TY2CP*6
TY2X15WP*6		1.521 [38,63]	.830 [21,08]			
TY2X2WP*6		2.034 [51,66]	1.249 [31,72]			
TY2X3WP*6		3.000 [76,2]	2.175 [55,25]	1.000 [25,4]		
TY2X4WP*6		4.332 [110,03]	3.487 [88,57]			
TY2X5WP*6		5.020 [127,51]	4.161 [105,69]			
TY25X2WP*6	2.750 [69,85]	2.034 [51,66]	1.249 [31,72]	.800 [20,32]	.300 [7,62]	TY25CP*6
TY25X3WP*6		3.000 [76,2]	2.175 [55,25]	1.000 [25,4]		
TY25X4WP*6		4.332 [110,03]	3.487 [88,57]			

* = COLOR CODE

B = BLACK G = GRAY I = INTRINSIC BLUE W = WHITE

Thomas & Betts
www.tnb.com

DESCRIPTION:

WIDE SLOT WIRING DUCT

SHEET NO:


4 OF 6

REV. NO:

2

DRAWING NO:

WSD-000180



CATALOG NO.	A (WIDTH)	B (HEIGHT)	C	D	F	COVER CATALOG NO.
TY3X1WP*6	3.250 [82,55]	1.055 [26,8]	.430 [10,92]	.800 [20,32]	.300 [7,62]	TY3CP*6
TY3X2WP*6		2.081 [52,86]	1.249 [31,72]			
TY3X3WP*6		3.056 [77,62]	2.175 [55,25]	1.000 [25,4]		
TY3X4WP*6		4.387 [111,43]	3.487 [88,57]			
TY3X5WP*6		5.061 [128,55]	4.161 [105,69]	1.333 [33,86]		
TY4X15WP*6	4.250 [107,95]	1.567 [39,8]	.830 [21,08]	.800 [20,32]	.300 [7,62]	TY4CP*6
TY4X2WP*6		2.081 [52,86]	1.249 [31,72]			
TY4X3WP*6		3.056 [77,62]	2.175 [55,25]	1.000 [25,4]		
TY4X4WP*6		4.387 [111,43]	3.487 [88,57]			
TY4X5WP*6		5.061 [128,55]	4.161 [105,69]	1.333 [33,86]		
TY6X4WP*6	6.250 [158,75]	4.387 [111,43]	3.487 [88,57]	.800 [20,32]	.300 [7,62]	TY6CP*6

* = COLOR CODE

B = BLACK G = GRAY I = INTRINSIC BLUE W = WHITE

Thomas & Betts
www.tnb.com

DESCRIPTION:

WIDE SLOT WIRING DUCT

SHEET NO:

5 OF 6

REV. NO:

2

DRAWING NO:

WSD-000180

NOMINAL DUCT SIZE		AREA SQUARE	ELECTRICAL												DATA CABLE			
			8 AWG		10 AWG		12 AWG		14 AWG		16 AWG		18 AWG		22 AWG		24 AWG	
			Ø.216	THHN	Ø.153	THHN	Ø.122	THHN	Ø.105	THHN	Ø.096	THHN	Ø.084	THHN	Ø.065	MTW	Ø.217	UTP/CM CAT6
W	H																UTP/CM CAT5E	UTP/CM
.75 x 1.00		.750	5	9	14	9	14	9	19	19	23	14	30	17	51	5	3	1
.75 x 1.50		1.125	7	14	22	13	22	13	29	29	35	21	46	25	76	7	5	2
.75 x 2.00		1.500	9	18	29	17	29	17	39	39	47	27	61	34	101	9	7	2
1.00 x 1.00		1.000	6	12	19	11	19	11	26	26	31	18	40	22	68	6	5	2
1.00 x 1.50		1.500	9	18	29	17	29	17	39	39	47	27	61	34	101	9	7	2
1.00 x 2.00		2.000	12	24	38	23	38	23	52	52	62	37	81	45	135	12	9	3
1.00 x 3.00		3.000	18	37	58	34	58	34	78	78	93	55	121	67	203	18	14	5
1.00 x 4.00		4.000	24	49	77	46	77	46	104	104	124	73	162	90	270	24	18	6
1.50 x 1.00		1.500	9	18	29	17	29	17	39	39	47	27	61	34	101	9	7	2
1.50 x 1.50		2.250	14	27	43	26	43	26	58	58	70	41	91	50	152	14	10	4
1.50 x 2.00		3.000	18	37	58	34	58	34	78	78	93	55	121	67	203	18	14	5
1.50 x 3.00		4.500	28	55	86	52	86	52	117	117	140	82	182	101	304	27	21	7
1.50 x 4.00		6.000	37	73	115	69	115	69	155	155	186	110	243	134	406	36	27	10
2.00 x 1.00		2.000	12	24	38	23	38	23	52	52	62	37	81	45	135	12	9	3
2.00 x 1.50		3.000	18	37	58	34	58	34	78	78	93	55	121	67	203	18	14	5
2.00 x 2.00		4.000	24	49	77	46	77	46	104	104	124	73	162	90	270	24	18	6
2.00 x 3.00		6.000	37	73	115	69	115	69	155	155	186	110	243	134	406	36	27	10
2.00 x 4.00		8.000	49	98	154	92	154	92	207	207	248	146	324	179	541	49	37	13
2.00 x 5.00		10.000	61	122	192	114	192	114	259	259	310	183	405	224	676	61	46	16
2.50 x 2.00		5.000	31	61	96	57	96	57	130	130	155	91	202	112	338	30	23	8
2.50 x 3.00		7.500	46	92	144	86	144	86	194	194	233	137	304	168	507	46	34	12
2.50 x 4.00		10.000	61	122	192	114	192	114	259	259	310	183	405	224	676	61	46	16
3.00 x 1.00		3.000	18	37	58	34	58	34	78	78	93	55	121	67	203	18	14	5
3.00 x 2.00		6.000	37	73	115	69	115	69	155	155	186	110	243	134	406	36	27	10
3.00 x 3.00		9.000	55	110	173	103	173	103	233	233	279	165	364	201	609	55	41	14
3.00 x 4.00		12.000	73	146	230	137	230	137	311	311	372	219	486	269	811	73	55	19
3.00 x 5.00		15.000	92	183	288	172	288	172	389	389	465	274	607	336	1014	91	69	24
4.00 x 1.50		6.000	37	73	115	69	115	69	155	155	186	110	243	134	406	36	27	10
4.00 x 2.00		8.000	49	98	154	92	154	92	207	207	248	146	324	179	541	49	37	13
4.00 x 3.00		12.000	73	146	230	137	230	137	311	311	372	219	486	269	811	73	55	19
4.00 x 4.00		16.000	98	195	307	183	307	183	415	415	496	293	648	358	1082	97	73	26
4.00 x 5.00		20.000	122	244	384	229	384	229	518	518	620	366	810	448	1352	121	91	32
6.00 x 4.00		24.000	147	293	461	275	461	275	622	622	744	439	912	537	1623	146	110	39
NOTE: WIRE FILL IS BASED ON 50% FILL OF DUCT AREA																		

Thomas & Betts
www.tnb.com

DESCRIPTION:

WIDE SLOT WIRING DUCT

SHEET NO:

6 OF 6

REV. NO:

2

DRAWING NO:

WSD-000180