

Eaton U57

Catalog Number: U57

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1-1/2"

General specifications



Photo is representative

| | |
|---|----------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body | U57 |
| | UPC |
| | 662276465824 |
| Product Length/Depth | Product Height |
| 15.13 in | 7.19 in |
| Product Width | Product Weight |
| 2.88 in | 6.2 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3

4

12

Product specifications

Shape

U

Trade size

1-1/2"

Material

Feraloy iron alloy

Resources

3D CAD drawing package

[Eaton Crouse-Hinds U57 3D drawing](#)

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

Installation instructions

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Eaton Specification Sheet - U57](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are
property of their respective



Powering Business Worldwide



Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton U57

Catalog Number: U57

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1-1/2"

General specifications



Photo is representative

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body | U57 |
| | UPC |
| | 662276465824 |
| Product Length/Depth | Product Height |
| 15.13 in | 7.19 in |
| Product Width | Product Weight |
| 2.88 in | 6.2 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3

4

12

Product specifications

Shape

U

Trade size

1-1/2"

Material

Feraloy iron alloy

Resources

3D CAD drawing package

[Eaton Crouse-Hinds U57 3D drawing](#)

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

Installation instructions

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Eaton Specification Sheet - U57](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are
property of their respective



Powering Business Worldwide



Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)