

Specifications

Photo is representative

Eaton UASTS131C226CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, 13-jaw, 3-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 4-wire, Ringless, 600 Vac

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton meter socket |
| CATALOG NUMBER | UASTS131C226CH |
| UPC | 786685216409 |
| PRODUCT LENGTH/DEPTH | 4.35 in |
| PRODUCT HEIGHT | 20 in |
| PRODUCT WIDTH | 12 in |
| PRODUCT WEIGHT | 18 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| CERTIFICATIONS | UL Listed |

Product specifications

| | |
|--------------------|---------------------------|
| TYPE | Instrument rated socket |
| AMPERAGE RATING | 20A |
| FEED TYPE | Top/bottom |
| NUMBER OF JAWS | 13-jaw |
| PHASE | Three-phase |
| ENCLOSURE MATERIAL | Aluminum |
| NUMBER OF WIRES | Four-wire |
| HUB TYPE | 3-5/16 in hub cover plate |
| SECURITY | Ringless |
| VOLTAGE RATING | 600 V |
| ACCESSORIES | Factory wired test switch |
| NUMBER OF SOCKETS | 1 |

Resources

| | |
|-------------------------------|---|
| CATALOGS | Residential and Light Commercial, Metering Products, Volume 1 Tab 4 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - UASTS131C226CH |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton UASTS131C226CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, 13-jaw, 3-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 4-wire, Ringless, 600 Vac

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton meter socket |
| CATALOG NUMBER | UASTS131C226CH |
| UPC | 786685216409 |
| PRODUCT LENGTH/DEPTH | 4.35 in |
| PRODUCT HEIGHT | 20 in |
| PRODUCT WIDTH | 12 in |
| PRODUCT WEIGHT | 18 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| CERTIFICATIONS | UL Listed |

Product specifications

| | |
|--------------------|---------------------------|
| TYPE | Instrument rated socket |
| AMPERAGE RATING | 20A |
| FEED TYPE | Top/bottom |
| NUMBER OF JAWS | 13-jaw |
| PHASE | Three-phase |
| ENCLOSURE MATERIAL | Aluminum |
| NUMBER OF WIRES | Four-wire |
| HUB TYPE | 3-5/16 in hub cover plate |
| SECURITY | Ringless |
| VOLTAGE RATING | 600 V |
| ACCESSORIES | Factory wired test switch |
| NUMBER OF SOCKETS | 1 |

Resources

| | |
|-------------------------------|---|
| CATALOGS | Residential and Light Commercial, Metering Products, Volume 1 Tab 4 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - UASTS131C226CH |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

