

Specifications



Photo is representative



Eaton UASTS131C226CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, 13-jaw, 3-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 4-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UASTS131C226CH
UPC	786685216409
PRODUCT LENGTH/DEPTH	4.35 in
PRODUCT HEIGHT	20 in
PRODUCT WIDTH	12 in
PRODUCT WEIGHT	18 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Instrument rated socket
AMPERAGE RATING	20A
FEED TYPE	Top/bottom
NUMBER OF JAWS	13-jaw
PHASE	Three-phase
ENCLOSURE MATERIAL	Aluminum
NUMBER OF WIRES	Four-wire
HUB TYPE	3-5/16 in hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
ACCESSORIES	Factory wired test switch
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UASTS131C226CH

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton UASTS131C226CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, 13-jaw, 3-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 4-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UASTS131C226CH
UPC	786685216409
PRODUCT LENGTH/DEPTH	4.35 in
PRODUCT HEIGHT	20 in
PRODUCT WIDTH	12 in
PRODUCT WEIGHT	18 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Instrument rated socket
AMPERAGE RATING	20A
FEED TYPE	Top/bottom
NUMBER OF JAWS	13-jaw
PHASE	Three-phase
ENCLOSURE MATERIAL	Aluminum
NUMBER OF WIRES	Four-wire
HUB TYPE	3-5/16 in hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
ACCESSORIES	Factory wired test switch
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UASTS131C226CH

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

