

Specifications

Eaton UGHTRS213CE



Photo is representative

Eaton meter socket, 1-pos resi service, 200A, Over/under, Hub cover plate, #6-350 kcmil, 5-jaw, 1-ph, #6-350 kcmil, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, Gnded 5th terminal (9 o'clock position), 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UGHTRS213CE
UPC	786685217918
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	15.13 in
PRODUCT WIDTH	11.25 in
PRODUCT WEIGHT	13 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Single-position residential service
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Five-jaw
PHASE	Single-phase
GROUND	Triplex
TERMINALS	Grounded fifth terminal (9 o'clock position)
UTILITY APPROVALS	WI : Madison Gas and Electric (MGE)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	Hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Horn
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UGHTRS213CE

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton UGHTRS213CE



Photo is representative

Eaton meter socket, 1-pos resi service, 200A, Over/under, Hub cover plate, #6-350 kcmil, 5-jaw, 1-ph, #6-350 kcmil, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, Gnded 5th terminal (9 o'clock position), 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UGHTRS213CE
UPC	786685217918
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	15.13 in
PRODUCT WIDTH	11.25 in
PRODUCT WEIGHT	13 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Single-position residential service
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Five-jaw
PHASE	Single-phase
GROUND	Triplex
TERMINALS	Grounded fifth terminal (9 o'clock position)
UTILITY APPROVALS	WI : Madison Gas and Electric (MGE)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	Hub cover plate
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Horn
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UGHTRS213CE

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

