

Specifications



Eaton UHTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-ph, #8-2/0 AWG, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UHTRS101BE
UPC	786685217734
PRODUCT LENGTH/DEPTH	3.61 in
PRODUCT HEIGHT	11.05 in
PRODUCT WIDTH	8.22 in
PRODUCT WEIGHT	6.7 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications	
TYPE	Single-position residential service
AMPERAGE RATING	125A
FEED TYPE	Overhead
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	NY : Central Hudson Gas & Electric (CHG&E) OH : Dayton Power and Light (DP&L) MD : First Energy (Potomac Edison) VA : First Energy (Potomac Edison) WV : First Energy (Mon Power) NJ : First Energy (Jersey Central Power and Light) OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company) PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power) WI : Madison Gas and Electric (MGE) IN : Northern Indiana Public Service Company (NIPSCO) WI : WE Energies / Wisconsin Public Service (WPS) NY : Rochester Gas & Electric (RG&E) NY : New York State Electric & Gas (NYSEG)
LINE	#8-2/0 AWG
LOAD	#8-2/0 AWG
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Horn
NUMBER OF SOCKETS	1

Resources	
CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UHTRS101BE

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton UHTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-ph, #8-2/0 AWG, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UHTRS101BE
UPC	786685217734
PRODUCT LENGTH/DEPTH	3.61 in
PRODUCT HEIGHT	11.05 in
PRODUCT WIDTH	8.22 in
PRODUCT WEIGHT	6.7 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications	
TYPE	Single-position residential service
AMPERAGE RATING	125A
FEED TYPE	Overhead
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	NY : Central Hudson Gas & Electric (CHG&E) OH : Dayton Power and Light (DP&L) MD : First Energy (Potomac Edison) VA : First Energy (Potomac Edison) WV : First Energy (Mon Power) NJ : First Energy (Jersey Central Power and Light) OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company) PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power) WI : Madison Gas and Electric (MGE) IN : Northern Indiana Public Service Company (NIPSCO) WI : WE Energies / Wisconsin Public Service (WPS) NY : Rochester Gas & Electric (RG&E) NY : New York State Electric & Gas (NYSEG)
LINE	#8-2/0 AWG
LOAD	#8-2/0 AWG
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Horn
NUMBER OF SOCKETS	1

Resources	
CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UHTRS101BE

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

