



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNF905 3-1/2" Female Union *Crouse-Hinds*

Catalog Number	UNF905
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Unf Union, Rigid/Imc, Female, Feraloy Iron Alloy, Group B Rated, 3-1/2"
Weight per unit	8.9 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Female Threaded, Female Threaded
dimensions	4.1300 IN X 5.6900 IN X 5.6900 IN

Descriptions

Description	3-1/2" FEMALE UNION
extra long description	CRS-H UNF905 3 1/2 FEMALE UNF UNION
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series UNF union, Rigid/IMC, Female, Feraloy iron alloy, Group B rated, 3-1/2"
Product Type	3 1/2 Female Unf Union
Special Features	5-11/16 In Diameter X 4-1/8 In Length

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274644707
Manufacturers Part Number	UNF905
UPC	782274644707

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Union

Packaging

Carton	1
Weight Per each	8.8999



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2
.....	Group F G, Class III
standard	UL 886, CSA C22.2