

Eaton UNRRS213BEUSE

Catalog Number: UNRRS213BEUSE

Eaton meter socket, 3 5/16 in hub opening, 200A, Overhead, Hub opening, #6-350 kcmil, Four-jaw, Single-phase, #6-350 kcmil, Sockets:1, Three-wire, Ring, 600V



General specifications

Product Name

Eaton meter socket

Catalog Number

UNRRS213BEUSE

UPC

786685217888

Product Length/Depth

4.48 in

Product Height

15.11 in

Product Width

11.22 in

Product Weight

18 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

3 5/16 in hub opening

Amperage Rating

200A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

TX : CenterPoint Energy (HL&P/Reliant)

Line

#6-350 kcmil

Load

#6-350 kcmil

Enclosure material

16 GA GALV STEEL

Number of wires

Three-wire

Hub type

Hub opening

Security

Ring

Voltage rating

600 V

Number of sockets

1

Resources

Specifications and datasheets

[Eaton Specification Sheet - UNRRS213BEUSE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton UNRRS213BEUSE

Catalog Number: UNRRS213BEUSE

Eaton meter socket, 3 5/16 in hub opening, 200A, Overhead, Hub opening, #6-350 kcmil, Four-jaw, Single-phase, #6-350 kcmil, Sockets:1, Three-wire, Ring, 600V



General specifications

Product Name

Eaton meter socket

Catalog Number

UNRRS213BEUSE

UPC

786685217888

Product Length/Depth

4.48 in

Product Height

15.11 in

Product Width

11.22 in

Product Weight

18 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

3 5/16 in hub opening

Amperage Rating

200A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

TX : CenterPoint Energy (HL&P/Reliant)

Line

#6-350 kcmil

Load

#6-350 kcmil

Enclosure material

16 GA GALV STEEL

Number of wires

Three-wire

Hub type

Hub opening

Security

Ring

Voltage rating

600 V

Number of sockets

1

Resources

Specifications and datasheets

Eaton Specification Sheet - UNRRS213BEUSE



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)