



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## UNY014 6" Male Union *Crouse-Hinds*

Catalog Number	UNY014
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Uny Union, Rigid/Imc, Male, Feraloy Iron Alloy, 6"
Weight per unit	21.5 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Male Threaded, Male Threaded
dimensions	6.1300 IN X 9.3100 IN X 9.3100 IN

### Descriptions

Description	6" MALE UNION
extra long description	CRS-H UNY014 6 NPT MALE UNY UNION
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series UNY union, Rigid/IMC, Male, Feraloy iron alloy, 6"
Product Type	6 NPT Male Uny Union
Special Features	9-5/16 In Diameter X 5-3/8 In Length

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274647708
Manufacturers Part Number	UNY014
UPC	782274647708

### Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Union

### Packaging

Carton	1
Weight Per each	21.45



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2