



URS101BCH Ringless Type No By Pass 100A Enc Meter Socket

Eaton Corp

Catalog Number	URS101BCH
Manufacturer	Eaton Corp
Description	Meter Socket, 125 A, 10.88 In Overall Height, 8 In Overall Width, 3.5 In Overall Length, Top/Bottom Mount, 1 Phase, 3-5/16 In Opening Hub, 4 Jaws, 3 Wires, 600 V, #8 to 2/0 Awg Wire Size, Overhead Feed, 7 LB
Weight per unit	7.0 (lbs/each)
Product Category	Residential Single Meter Socke

Features

amperage rating	125
dimensions	3.5000 IN X 8.0000 IN X 10.8800 IN
Phase	1
Voltage Rating	600 V

Descriptions

Also Known As...	Meter Socket
	Meter Box
Description	RINGLESS TYPE NO BY PASS 100A ENC METER SOCKET
extra long description	ETN URS101BCH MtrSkt,125A,Ringless,

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114003985
UPC	782114003985

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Meter socket

Packaging

Carton	1
Weight Per each	7

Uses, Certifications, and Standards

standard	UL Listed
----------	-----------