

# Specifications



## Eaton UTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

### General specifications

|                             |  |
|-----------------------------|--|
| <b>PRODUCT NAME</b>         | Eaton meter socket   |
| <b>CATALOG NUMBER</b>       | UTRS101BE  |
| <b>UPC</b>                  | 786685217710   |
| <b>PRODUCT LENGTH/DEPTH</b> | 3.61 in  |
| <b>PRODUCT HEIGHT</b>       | 11.05 in   |
| <b>PRODUCT WIDTH</b>        | 8.22 in  |
| <b>PRODUCT WEIGHT</b>       | 6.46 lb  |
| <b>WARRANTY</b>             | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| <b>CERTIFICATIONS</b>       | UL Listed  |

## Product specifications

|                          |   |
|--------------------------|---|
| <b>TYPE</b>              | Single-position residential service   |
| <b>AMPERAGE RATING</b>   | 125A  |
| <b>FEED TYPE</b>         | Overhead  |
| <b>NUMBER OF JAWS</b>    | Four-jaw  |
| <b>PHASE</b>             | Single-phase  |
| <b>UTILITY APPROVALS</b> | ME : Central Maine Power<br>NM : El Paso Electric<br>TX : El Paso Electric<br>AL : Alabama Power<br>ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)<br>MO : Empire District Electric<br>OK : Empire District Electric<br>AR : Entergy<br>LA : Entergy<br>MS : Entergy<br>TX : Entergy<br>AL : Huntsville Utilities<br>FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br>IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br>KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br>NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br>OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br>SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br>TX : Pedernales Electric |

## Resources

|                                      |   |
|--------------------------------------|---|
| <b>CATALOGS</b>                      | <a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a> |
| <b>SPECIFICATIONS AND DATASHEETS</b> | <a href="#">Eaton Specification Sheet - UTRS101BE</a>                               |

|                   |   |
|-------------------|---|
|                   | Cooperative<br>NM : Public Service<br>Company of New Mexico<br>(PNM)<br>SC : South Carolina Electric<br>and Gas (SCE&G) |
| LINE              | #8-2/0 AWG  |
| LOAD              | #8-2/0 AWG  |
| NUMBER OF WIRES   | Three-wire  |
| HUB TYPE          | 3-5/16 in hub opening   |
| CONNECTION        | Ground connection   |
| SECURITY          | Ringless  |
| VOLTAGE RATING    | 600 V   |
| NUMBER OF SOCKETS | 1   |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| DATE:           |



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton UTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

### General specifications

|                             |  |
|-----------------------------|--|
| <b>PRODUCT NAME</b>         | Eaton meter socket   |
| <b>CATALOG NUMBER</b>       | UTRS101BE  |
| <b>UPC</b>                  | 786685217710   |
| <b>PRODUCT LENGTH/DEPTH</b> | 3.61 in  |
| <b>PRODUCT HEIGHT</b>       | 11.05 in   |
| <b>PRODUCT WIDTH</b>        | 8.22 in  |
| <b>PRODUCT WEIGHT</b>       | 6.46 lb  |
| <b>WARRANTY</b>             | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| <b>CERTIFICATIONS</b>       | UL Listed  |



Powering Business Worldwide

## Product specifications

|                          |  |
|--------------------------|--|
| <b>TYPE</b>              | Single-position residential service  |
| <b>AMPERAGE RATING</b>   | 125A   |
| <b>FEED TYPE</b>         | Overhead   |
| <b>NUMBER OF JAWS</b>    | Four-jaw   |
| <b>PHASE</b>             | Single-phase   |
| <b>UTILITY APPROVALS</b> | <p>ME : Central Maine Power<br/> NM : El Paso Electric<br/> TX : El Paso Electric<br/> AL : Alabama Power<br/> ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)<br/> MO : Empire District Electric<br/> OK : Empire District Electric<br/> AR : Entergy<br/> LA : Entergy<br/> MS : Entergy<br/> TX : Entergy<br/> AL : Huntsville Utilities<br/> FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br/> IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br/> KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br/> NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br/> OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br/> SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)<br/> TX : Pedernales Electric</p> |

## Resources

|                                      |   |
|--------------------------------------|---|
| <b>CATALOGS</b>                      | <a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a> |
| <b>SPECIFICATIONS AND DATASHEETS</b> | <a href="#">Eaton Specification Sheet - UTRS101BE</a>                               |

|                   |   |
|-------------------|---|
|                   | Cooperative<br>NM : Public Service<br>Company of New Mexico<br>(PNM)<br>SC : South Carolina Electric<br>and Gas (SCE&G) |
| LINE              | #8-2/0 AWG  |
| LOAD              | #8-2/0 AWG  |
| NUMBER OF WIRES   | Three-wire  |
| HUB TYPE          | 3-5/16 in hub opening   |
| CONNECTION        | Ground connection   |
| SECURITY          | Ringless  |
| VOLTAGE RATING    | 600 V   |
| NUMBER OF SOCKETS | 1   |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| DATE:           |



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.

