

# Specifications

Photo is representative



## Eaton V48M28T2216

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, FR944, 220°C, 225 kVA, Fl/wall mt uprt, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 150°C, 225 kVA, WS61, 280B

### Physical Attributes

<b>COIL MATERIAL</b>	Aluminum
<b>ENCLOSURE</b>	NEMA 2
<b>FRAME</b>	FR944
<b>INSULATION</b>	220 °C
<b>MOUNTING</b>	Floor or wall, upright only
<b>TAP SIZE</b>	2 at +2.5%, 4 at -2.5%
<b>TYPE</b>	Energy-efficient ventilated dry-type transformer
<b>WIRING CONNECTION</b>	280B

### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose ventilated transformer
<b>CATALOG NUMBER</b>	V48M28T2216
<b>UPC</b>	786680147289
<b>PRODUCT LENGTH/DEPTH</b>	33.5 in
<b>PRODUCT HEIGHT</b>	60 in
<b>PRODUCT WIDTH</b>	38 in
<b>PRODUCT WEIGHT</b>	1571 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	DOE2016 Efficient
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	10 CFR Part 431 (2016) Efficient

# Specifications

Photo is representative



## Eaton V48M28T2216

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, FR944, 220°C, 225 kVA, Fl/wall mt uprt, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 150°C, 225 kVA, WS61, 280B

### Physical Attributes

<b>COIL MATERIAL</b>	Aluminum
<b>ENCLOSURE</b>	NEMA 2
<b>FRAME</b>	FR944
<b>INSULATION</b>	220 °C
<b>MOUNTING</b>	Floor or wall, upright only
<b>TAP SIZE</b>	2 at +2.5%, 4 at -2.5%
<b>TYPE</b>	Energy-efficient ventilated dry-type transformer
<b>WIRING CONNECTION</b>	280B

### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose ventilated transformer
<b>CATALOG NUMBER</b>	V48M28T2216
<b>UPC</b>	786680147289
<b>PRODUCT LENGTH/DEPTH</b>	33.5 in
<b>PRODUCT HEIGHT</b>	60 in
<b>PRODUCT WIDTH</b>	38 in
<b>PRODUCT WEIGHT</b>	1571 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	DOE2016 Efficient
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	10 CFR Part 431 (2016) Efficient