



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VC150IM12 150W CLG MNT V/T Fix *Lithonia Lighting*

Catalog Number	VC150IM12
Manufacturer	Lithonia Lighting
Description	Utility Ceiling-Mounted Fixtures For Entrances, Hallways, Closets, Tunnels or Other Utility Applications
Weight per unit	2.5 (lbs/each)
Product Category	Incandescent Vapor Tight Light

Features

average life	100,000
Ballast Type	Not Applicable
Hardware	Yes
Lamp Included	NO
Lamp Type	Incandescent
Material	Aluminum
Number of Lamps	1
pallet quantity	288
Power Source	Hardwired
Shape	Round
Socket Type	Medium: Screw
Voltage Rating	120
Warranty	2
Wattage	150

Material, Color, and Finish

Color	Gray
Finish	Gloss
fixture material	aluminum
Lens Material	Glass
Style	Traditional

Dimensions and Weight

Height	9.0000
Length	4.5000
Width	4.5000



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	150W CLG MNT V/T FIX
extra long description	LITH VC150I M12 Utility vapor tight
Long Description	Utility ceiling-mounted fixtures for entrances, hallways, closets, tunnels or other utility applications
Product Type	Wallpack
Special Features	Utility wall-, ceiling- or pendant-mounted fixtures for entrances, hallways, closets, tunnels or other utility applications. Incandescent, fluorescent, metal halide or high pressure sodium sources are available.

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00745973817704
Manufacturers Part Number	VC150IM12
UPC	745973817704

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	Wall Pack

Packaging

Carton	1
Package	12
Weight	2.0000
Weight Per each	2.5

Uses, Certifications, and Standards

Application	Education,Hospitality,Offices & Banks
environmental conditions	OUTDOOR
Mounting	SURFACE
standard	cUL